

SOLID PC 1919 18 G



Sample photo

Order symbol: PC 1919 18 G
Product nbr: 5330369
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074005427
El. number:
Finland: 3423703
Italy: 7401015
Sweden: 2539408

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		188	188	180	Ingress Protection (EN 60529): IP 66/67
inch:		7.4	7.4	7.1	Impact Resistance (EN 62262): IK 08/09
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 5V
Cover screws material:		Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:		Grey			NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12
Gasket material:		Polyurethane			Certificates:
Temperatures:					Underwriters Laboratories
Short term:		-40 ... 120 °C			Fimko
Continuous:		-40 ... 80 °C			Europe EN 62208: 2003
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
EKHVT		Mounting plate			
EKV 12		DIN-35 Mounting rail			

