

BS 4808 0.22mm²



Part NO: RGW-883

Product Code: BS 4808 0.22mm² Part 2 Class 2

Product Description

Reference Standard

Customer's sample spec. and the general standard

Multi-construction

1

Cable Construction

Conductor	Tinned Copper
square(mm ²)	0.22
Construction	T0.20±0.008×7
Standard Dia.(mm)	0.60
Insulation	PVC
Thickness	0.3
Insulation Dia.(±0.1mm)	1.20
Insulation Color	According to the customer

Marking

According to the customer

PACKAGING


100M/Reel

500M/Reel

Revision History

A0-1

Design



Electrical Characteristics

Max. Conductor DC Resistance at 20°C (Ω /Km)	<86.2
Min. Insulation DC Resistance at 20°C (MΩ *Km)	200
Rated Temperature(°C)	85
Rated Voltage (V)	1000

RoHS GUIDELINE

We operate according to the following standards

Control Item	Standard	Testing Method	Testing Equipment
Cadmium content (Cd)	<0.01%	EN1122	ICP-AES
Lead content (Pb)	<0.1%	EPA3050B	ICP-AES
Mercury content (Hg)	<0.1%	EPA3052	ICP-AES
Chromium (VI) content	<0.1%	EPA3060(UN-VIS)	ICP-AES
Polybrominated Biphenyls (PBB)	Forbidden	GC/MS	/
Polybrominated Diphenyl Ether (PBDE)	Forbidden	GC/MC	/

Date: 2008-08-06

Page: 1 / 1