



ENGLISH

Datasheet

Stock No: 459-799

# RS Pro 38 Series Red Insulated Crimp Receptacle, 2.8 x 0.5mm, 22 → 16 AWG, Tin Plated



## Product Details

### RS Shrouded Receptacles

A range of fully insulated shrouded female disconnect crimp receptacles with a copper sleeve and a choice of insulation types as follows:

Part numbers ending in 'VH' have a flared vinyl insulation

Part numbers ending in 'FEH' have funnel entry polycarbonate insulation

These insulated shrouded female disconnect crimp receptacles are available with a various wire ranges and tab sizes.

Red 0.5 - 1.5 mm<sup>2</sup>

Blue 1.5 - 2.5 mm<sup>2</sup>

Yellow 2.5 - 6.5 mm<sup>2</sup>

### RS Pro Range

Conversion table	
M3 / 6 BA	M5/ 2BA
M3.5/ 4BA	M6/ 0BA
M4/ 3BA	

Wire Sizes	
Mini Yellow	0.2 - 0.5 mm <sup>2</sup>
Red	0.5 - 1.5 mm <sup>2</sup>
Blue	1.5 - 2.5 mm <sup>2</sup>
Yellow	2.5 - 6.5 mm <sup>2</sup>

Technical Specification	
Temperature rating	+70°C
Body Material	Copper
Body Plating	Tin



ENGLISH

## Specifications:

Tab Size	2.8 x 0.5mm
Colour	Red
Insulation	Insulated
Wire Size	22 → 16 AWG
Gender	Female
Connector Type	Tab
Series	38
Contact Material	Brass
Contact Plating	Tin
Length	19mm
Insulation Material	Polycarbonate