

## 30 Amp L2130 Plug - Black Back, White Front Body

L2130P



Turnlok Plug 5wire 30amp 3phase  
120/208v



### features & benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

### specifications

#### General Info

Color: Black, White  
Type: Plug  
Number Of Wires: 5

### **Listing Agencies/Third Party Information**

CSA Standard: Yes  
Federal Spec: Yes  
Fed Spec Number: WC596  
UL Listing No: 498  
UL Standard: Yes  
UN SPS C: 39121403

### **Dimensions**

Diameter U S: 2.20"  
Length U S: 3.75"

### **Technical Information**

Amps: 30 Amp  
NEMA Configuration Number: L2130  
Volts: 120/208V  
Volts A C: 120/208

### **Buy American Act Compliance**

Country of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant