

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [84729-0004](#)  
**Status:** **Active**  
**Overview:** Sealed Industrial USB Solutions  
**Description:** Sealed Industrial USB Type A Plug-to-Shielded Pigtail, 0.80m (2.62') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-84727-002 \(PDF\)](#)

**General**

Product Family	Industrial Receptacles
Series	<a href="#">84729</a>
IP Rating	IP67
Overview	<u>Sealed Industrial USB Solutions</u>
Product Name	RJ45
Type	Single Ended (pigtail)
UPC	822348832002

**Physical**

Coupling Type	Overmolded Cable
Gender	Female
Keyway	N/A
Length	N/A
Material - Component	Nylon
Mounting Thread Size	N/A
Orientation	N/A
Panel Mount	N/A
Poles	4
Temperature Range - Operating	-20°C to +60°C
Wire Size AWG	28
Wire/Cable Type	USB

**Electrical**

Current - Maximum per Contact	1A
Voltage - Maximum	30V AC (RMS)

**Material Info**

**Reference - Drawing Numbers**

Product Specification	PS-84727-002
Sales Drawing	SD-84729-006



*image - Reference only*

**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC**

Not Reviewed

**Low-Halogen Status**

**Not Low-Halogen**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of  
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

**Search Parts in this Series**

[84729Series](#)

**Mates With**

[84727 Sealed Industrial USB 2.0 Type A  
 Plug to Shielded Pigtail Receptacles](#)