






NOTES:

- (SECT)
1. PRODUCT SPEC, :108-5410
 2. APPLICABLE CONTACT P/N
TAB CONTACT:177917-□(°20-°16AWG)
 ,177916-□(°26-°22AWG)
 3. MATING CONN,P/N
PLUG HSG.177899-□;
REC CONTACT:177915-□(°20-°16AWG)
 177914-□(°26-°22AWG)
 - 4.APPLICABLE PLATE P/N:177919-□
 5. INSTRUCTION SHEET : 411-5638
 6. APPLICABLE PANEL THICKNESS : 0.8-2.0 (SEE FIG 1)
 7. INSERT CONN.FROM PRESS DIRECTION SIDE FOR METAL PANEL.
 8. EDGE OF THICKNESS WAY MUST NOT ROUND FOR MOLDED PANEL.

A. SEE TABLE 1

断面 "A" - "A"
(SECT)

回路番号
(CIRCUIT No.)

表1 (TABLE 1)

トレードマーク (TRADE MARK)	生産場所 (MANUFACTURING PLACE)
— —AMP OR AMP	日本 (JAPAN)
—+ —+AMP OR AMP	中国 (CHINA(PRC))
・ ・AMP OR AMP	韓国 (KOREA)

黒 (BLACK)	↑	↑	-9
青 (BLUE)			-6
黄 (YELLOW)			-4
赤 (RED)	↓	↓	-2
自然色 (NATURAL)	3		177907-1
ハウジング色調 (HOUSING COLOR)	種数 (Pos.)	型番 (P/N)	

				Copyright ©1993年 AMP (Japan), LTD. ALL RIGHTS RESERVED.				AMP Tyco Electronics AMP K.I. Kawasaki, Japan			
				適合電線断面積 (WIRE RANGE) 線径外径 (INSULATION DIA.) --- mm² (AWG) --- mmφ				名称 (NAME) アンブ パワー ダブルロック コネクタ 3極 3.96mmピッチ キャップ・ハウジング (パネル取付タイプ) AMP POWER DOUBLE LOCK CONN. 3.96mm PITCH CAP HOUSING 3 Pole (PANEL MOUNT)			
				材料 (MATERIAL) 仕上 (FINISH) 5/6 ナイロン (UL94V-0) 5/6 NYLON (UL94V-0)				一般公差 10mm以下: ±0.2 10mm以上 30mm以下: ±0.25 30mm以上 100mm以下: ±0.3 角 度: 23°			
				DR. 9. SEP. '93 DE. 9. SEP. '93 M. SUZUKI M. SUZUKI				尺度 (SCALE) REV. SHEET --- C 1 OF 1			
				CHK. 9. SEP. '93 APP. 9. SEP. '93 M. SHINDO Y. KASHIWA							
LTR 変更 (REVISION RECORD)				DR. CHK. DATE							
C	変更	(FJ00-2223-01)	auth	MS	24.09.91						
B	変更	(FJ00-0953-98)	T.Y	MS	27.09.91						
A	変更	(FJ00-0587-84)	H.S	H.S	18. MAY '94						
O	作成	(FJ00-0791-93)	H.S	H.S	8. SEP. '93						