




Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback

2TP66-1



Actual product appearance may vary.

TP Series Rocker Switch, 2 pole, 3 position, Screw terminal, Flush Panel Mounting

Features

- Environmentally sealed
- Two and three-position pushbutton action
- Various button colors
- 1, 2, and 4-pole circuitry
- Flush panel and above panel mountings
- Temperature range: -54 ° C to +71° C [-65 ° F to +160° F]
- UL recognized, CSA certified
- CE approved

Potential Applications

- Industrial machinery and equipment
- Military and commercial aviation
- Marine applications
- Construction equipment
- Test instruments
- Agricultural machinery
- Process control
- Medical instrumentation

Description

MICRO SWITCH™ TP Rocker switches may be mounted flush with panel for a low-button profile or above panel for a distinct button appearance. Buttons measure 22,1 mm x 37,1 mm [.87 in x 1.46 in]. They are removable and interchangeable, and come in transparent plastic, translucent plastic, and six colors of opaque plastic. Switches without buttons are also available, as well as separate buttons.

Supporting Documentation

- Accessory: Rocker Operator
- Engineering Drawing

Product Specifications			
Circuitry/Operating action	Keyway Position 1 2 3 6 5 4 ON	Center Position 1 2 3 6 5 4 OFF	Opposite Keyway Position 1 2 3 6 5 4 ON
Product Type	MICRO SWITCH™ Rocker		
Ampere/Voltage Range (Resistive Load)	0.5 A to 15 A at 0.5 Vac to 277 Vac,0.5 A to 20 A at 0.5 Vdc to 28 Vdc,0.5 A at 250 Vdc,0.75 A at 115 Vdc		
Circuitry	DPDT		
Action	3 position		
Mounting	Flush Panel		
Termination	Screw		
Button Type	Transparent		
UL/CSA Rating Code	L191: 15 A - 125, 250, 277 Vac; 1/2 Hp - 125 Vac; 1 Hp - 250, 277 Vac; 5 A - 120 Vac "L"		
Comment	Silver cadmium oxide contacts		
Availability	Global		
UNSPSC Code	302119		
UNSPSC Commodity	302119 Switches and controls and relays		
Series Name	TP		

My Links

- Login to iCOM
- Login as Rep/AD
- Login as Guest
- Login to Digital University

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

Specification Search