

15A/125V TradeMaster® Duplex Receptacle, Ivory

3232I



Our Pass & Seymour TradeMaster® receptacles combine a traditional look with reliable, time-tested operation for any residential application.

features & benefits

- Extra-long strap. Quickloop wire looping aid. Longer tri-drive screws for easier #12 AWG looping. Extra-large circuit break-off tabs.
- Side-access push wire release. Side wire accepts #12 - #14 AWG solid wire. Push wire accepts #14 AWG solid only.
- Low profile face. Traditional contoured face. (3232 models) Self-grounding models provide automatic ground clip.

specifications

General Info

Color: Ivory
Type: Duplex
Number Of Poles: 2

Listing Agencies/Third Party Information

CSA Listing Info: C22.2 No.42
CSA Standard: Yes
cULus: Yes
UL Listing No: UL498
UL Standard: Yes
UN SPS C: 39121406

Dimensions

Depth U S: .960"
Height U S: 3.31"
Width U S: 1.32"

Technical Information

Amps: 15
NEMA Configuration Number: 5-15R
NEMA Rating: Yes
Volts: 125
Volts A C: 125

Buy American Act Compliance

Country of Origin: CHINA
Buy American Act Status: No