



Y for performance classes 1,2 or 3
(contact cycle for G1/G2/G3 = 500/200/50)

No.	St.	Part	Type Description/Material	Surface plating/Colour/Class
5	2	Mounting screw	4-40 / Brass	nickel plated
4	2	Female screw lock	F-GSCH1/5-K441 / Steel	tin plated
3	1	Hood	FAW1 / Zinc die-cast	nickel plated
2	1	D-Sub Connector	F09S13RGY-2874	tin plated
1	1	D-Sub Connector	F09P13G0-2651	tin plated

TITLE		SCALE	
Shielded Right Angled Adapter		2:1	
Measurement without tolerance acc. to ISO 2768-m NAME / DATE bright finder 18-10-2011 DRAWN CHECKED isschref 19-10-2011			
ORIGINAL DIN A3-DRAWING AS A FILE		REPLACEMENT FOR:	
REV.	DATE	CH-NO.	DWG. NO.
1			FAW1PSGyU-4476
			REV. 1
			PAGES 1

