

MC612

General Information

Extended Product Type:	MC612
Product ID:	1SNK150000R0000
EAN:	3472591500004
Catalog Description:	MC612 Terminal Block Blank Marker card, white, polycarbonate
Long Description:	MC612 Terminal Block Blank Marker card, white, polycarbonate



Categories

Products » Low Voltage Products and Systems » Connection Devices » Markers and Marking Systems » Terminal Block Markers

Ordering

EAN:	3472591500004
Minimum Order Quantity:	22 piece
Customs Tariff Number:	39269097

Dimensions

Product Net Width:	6.0 mm
Product Net Height:	12.0 mm
Product Net Length:	5.6 mm
Product Net Depth:	5.6 mm
Product Net Weight:	10.00 g

Container Information

Package Level 1 Units:	22 piece
Package Level 1 Width:	120 mm
Package Level 1 Length:	200 mm
Package Level 1 Gross Weight:	0.22000 kg
Package Level 1 EAN:	3472591500004

Package Level 2 Units: 858 piece

Environmental

Ambient Air Temperature: Operation -55 +110 °C
Storage -55 +110 °C

Resistance to Vibrations acc. to IEC 60068-2-6: Compliant

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Technical UL/CSA

Flammability According to UL94: V0

Additional Information

Ambient Temperature: -5 +40 °C
Color: White
Function: Blank card
IIT Publishing Status: Level 0 - Information enabled
Insulation Material: Polycarbonate
Marketing Description: Blank card
Pollution Degree: 3
Product Main Type: MC612
Product Name: Marking
Product Type: Marker card
RoHS Date: 18 08 2005
Spacing: 6 mm
Sub-Function 2: In polycarbonate

Certificates and Declarations (Document Number)

Declaration of Conformity - CE: 1SND225156C1000
GOST Certificate: 1SND161005A1103
RoHS Information: 1SND230504F0204

Classifications

E-nummer: 2967591

ETIM 4.0: EC000761 - Labelling for terminal block

ETIM 5.0: EC000761 - Labelling for terminal block

Object Classification Code: X
