



GE
Lighting



GLS

TU 30W HALO A/CL/E27 240V GE TWBX
2/16TR

98365

Product information

GE's HaloGLS range is a direct replacement for regular incandescent lamps offering a crisp white light. Environmentally friendly solution for those who prefer light quality associated with incandescent bulbs.

- Last twice as long and consume up to 30% less electricity than corresponding incandescent lamps.
- Provide instant-on, full light output at start-up and lumens are maintained throughout the life of the product.
- Unlike some compact fluorescent products, these lamps are 100% retrofit with the incandescent lamps they replace.
- Can be used with dimming switches.
- Environmentally friendly with no lead or mercury.
- Up to 2,000 hours life
- Excellent colour rendering, light close to natural (100% CRI)

- More than 90% lumen maintenance over life
-

Product data

| | |
|-----------------------------|-----------------------|
| Cap/Base | E27 |
| Bulb Shape | GLS |
| Bulb Diameter [mm] | 50 |
| Dimming Capability | Yes |
| Maximum Overall Length [mm] | 89.5 |
| DUN Code | 10043168983652 |
| EAN Code | 0043168983655 |
| Net weight per piece [g] | 25 |
| Gross weight per piece [g] | 38 |
| Brand | General Electric (GE) |

Performance data

| | |
|---|-------|
| Nominal power [W] | 30 |
| Nominal lamp voltage [V] | 240 |
| Nominal lumens [lm] | 405 |
| Colour temperature [K] | 2800 |
| Colour Rendering Index (CRI) [Ra] | 100 |
| Rated Life [h] | 1000 |
| Energy efficiency class (EEC) | D |
| Weighted energy consumption [kWh/1000h] | 31.53 |

Logistic data

| | |
|--------------------------|-----------------------------|
| Pack Quantity | 16 |
| Inner pack type | TWIN BOX |
| Outer pack type | TRAY OUTER |
| Layer quantity | 384 EUR, 480 UK |
| Layer quantity EUR | 384 |
| Layer quantity UK | 480 |
| Pallet quantity EUR (PC) | 4224 |
| Pallet quantity UK (PC) | 5280 |
| Outer case size | 169 x 200 x 91 (mm) |
| Product status | Available while stock lasts |

Application areas



Downloads & Links

[Go to the catalog site \(HTTP\)](#)

[Halogen Lamps Spectrum Catalogue \(PDF\)](#)

[GLS, Candle, Spherical Lamps Data sheet \(PDF\)](#)

[Lighting design tools & calculators \(HTTP\)](#)

Disclaimer

Please note that the rated life of those lamps under this SKU number placed on the market on or before 31 August 2013 can be either 1,000 hours or 2,000 hours. The rated life of those lamps placed on the market on or after 1 September 2013 is exclusively 2,000 hours.