

30 Amp NEMA L530 Single Receptacle

L530R



Turnlok Receptacle Single 3wire 30amp
125v



features & benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

specifications

General Info

Type: Single, Receptacles
Number Of Wires: 3

Listing Agencies/Third Party Information

CSA Standard: Yes
CUL Listing No: No
cURus: No
Federal Spec: Yes
Fed Spec Number: WC596

UL Listing No: 498
UL Standard: Yes
UN SPS C: 39121403
UR: No

Dimensions

Depth U S: 1.28"
Height U S: 3.28"
Width U S: 1.62"

Technical Information

Amps: 30 Amp
NEMA Configuration Number: L530
Volts: 125V
Volts A C: 125

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant