

# 64 42 115

## Electronics End Cutting Nipper



- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Sturdy, zero backlash box joint
- Low-friction double spring for gentle and even opening
- The polish or mirror polish (only finish 2) together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutting edges additionally induction hardened, cutting edge hardness at least 56 HRC
- High-grade special tool steel, forged, multi stage oil-hardened
  - Style:Oblique End Cutter, short head, with small bevel,  $\alpha = 27^\circ$



<b>Article No.</b>	64 42 115
<b>EAN</b>	4003773040439
<b>Head</b>	mirror polished
<b>Handles</b>	with multi-component grips
<b>Style</b>	4
<b>Cutting capacities medium hard wire (diameter) Ø mm</b>	1,0
<b>Cutting capacities hard wire (diameter) Ø mm</b>	0,5
<b>Cutting capacities soft wire (diameter) Ø mm</b>	1,5
<b>B mm</b>	10,0
<b>D mm</b>	7,0
<b>C mm</b>	12,0
<b>A mm</b>	10,5
<b>Dimensions angle °</b>	27
<b>Length mm</b>	115
<b>Net weight g</b>	69

technical change and errors excepted

