Electronic housing - EMG 45-H 7,5MM KLAR - 2946214

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://download.phoenixcontact.com)

Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design.
Height: 7.5 mm

Key commercial data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	4 017918 082178
Weight per Piece (excluding packing)	9.1 g
Custom tariff number	85472000
Country of origin	Germany

Technical data

General

Housing type	Component housing
Housing material	Polycarbonate, PC
Color	transparent

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C

Dimensions

Length	38 mm
Constructional height	7.5 mm
Width	45 mm

Technical data

Inflammability class according to UL 94	V2
Number of positions	16

Classifications

eCl@ss

eCl@ss 4.0	27180401

Electronic housing - EMG 45-H 7,5MM KLAR - 2946214

Classifications

eCl@ss

eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC000886

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Phoenix Contact 2014 © - all rights reserved
http://www.phoenixcontact.com