


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL ISSUE	12 SEP 05	MGR	DB



NOTES:

- 1 ATTENUATION $\leq 0,3$ dB, MEASURED AT 1300nm ACC. TO IEC 61300-3-4 EQUILIBRIUM MODE CONDITION
- 2 SUPPLY FILLED OUT TEST RESULT SHEET WITH EACH INDIVIDUALLY PACKED ASSEMBLY

3 DAT LABEL INFO:

- UNIQUE SERIAL NUMBER
- TYCO LOGO PN
- MANUFACTURING LOCN.

4 CABLE INFO:

- CORE DIA - 50/125 μm
- OUTER DIA - 0,9 mm
- BUFFER COLOR - GREEN
- BUFFER MATERIAL - LSZH

PART NUMBER	"L" (Meter)
0-5349569-1	0,5 -0/+0,1
0-5349569-2	1,0 -0/+0,2
0-5349569-3	1,5 -0/+0,2
0-5349569-4	2,0 -0/+0,2
0-5349569-5	2,5 -0/+0,2
0-5349569-6	3,0 -0/+0,2
0-5349569-7	3,5 -0/+0,2
0-5349569-8	4,0 -0/+0,2
0-5349569-9	4,5 -0/+0,2
1-5349569-0	5,0 -0/+0,2
1-5349569-1	5,5 -0/+0,2
1-5349569-2	6,0 -0/+0,2
1-5349569-3	6,5 -0/+0,2
1-5349569-4	7,0 -0/+0,2
1-5349569-5	7,5 -0/+0,2
1-5349569-6	8,0 -0/+0,2
1-5349569-7	8,5 -0/+0,2
1-5349569-8	9,0 -0/+0,2
1-5349569-9	9,5 -0/+0,2
2-5349569-0	10,0 -0/+0,2

Qty	Part Number	Description	Item
1	-	DAT-85 LABEL 3	-
1	-	PROTECTIVE COVER, 2.5MM, BLACK	4
1	-	CONN,CER,BNT,UNI BODY,125 μm	3
1	-	BOOT,BARE FIBER,BLACK	2
L	-	FOCAB 0.9S 50/125 GREEN LSZH	1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	GIRIYAPPA. M	12 SEP 05	Tyco Electronics Corporation FOBU, Bangalore, India
CHK	DIWAKAR BELAVADI	12 SEP 05	
APVD	DIWAKAR BELAVADI	12 SEP 05	
PRODUCT SPEC			
APPLICATION SPEC			NAME
MATERIAL			SIZE
FINISH			CAGE CODE
WEIGHT			DRAWING NO
CUSTOMER DRAWING			RESTRICTED TO

SCALE: NTS SHEET 1 OF 1 REV A