

Datasheet

RS Pro Non-Fused Terminal Block, 3 Way/Pole, Screw Terminals, 2.5 mm² Panel Mount, PA, 450 V

RS Stock No: **868-0812**



Product Details

RS Pro non-fused terminal block in white colour, comes with direct fast clamp without wire protectors. This block with 3 ways, is made of polyamide material. This terminal block with 2.5-mm² wire, features screw termination. The panel mount block with nickel plated brass contact, has a voltage rating of 450 V.

Features and Benefits

- Self-extinguishing of UL 94 V-2, IEC 695-2-1 to 850°C, IEC 695-2-2
- Maximum operating temperature of 110°C
- Short-time temperature of 160°C
- Test voltage of 2500 V
- galvanised steel M 3 x 6 screws
- Suitable for panel with thickness: 0.6 to 1 mm
- Marking: L Earth and N on poles

**Specifications:**

Contact Material	Brass
Contact Plating	Nickel
Enclosed	No
Material	Polyamide
Maximum Operating Temperature	+110°C
Mounting Type	Panel Mount
Number of Ways	3
Pitch	21.5 mm
Termination Method	Screw
Voltage Rating	450 V
Wire Size	2.5 mm ²
Colour	White
Screw Size	M3 x 6
Standards Met	RoHS, UL 94V-2, IEC 695-2-1, IEC 695-2-2, EN 60998-1, EN 60998-2-1