

CabinetMate Plug-In Outlet Center Unit / 120V/15A/48" long/10 O/L /15' cord

4810ULBD



Ten outlets, 15' [4.6m] cord. Length 48" [1.2m]. Receptacle center-to-center 4" [101mm]. 15 Amp unit with a 15A resettable circuit breaker.

features & benefits



specifications

Technical Information

Amps: 15
Mounting: 0U
Rated Voltage: 120V
Number Of Circuits: 1
Receptacle Type: NEMA
Network Monitoring: No
Surge Suppression: Computer Grade
Number Of Outlets: 10

Buy American Act Compliance

Country of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant