

# DETA



# Metalclad

Essentials Product Catalogue 2014/2015

# Metalclad

Socket Outlets

Plate Switches

Connection Units

Double Pole Switches

Data Plate

Back Boxes

# Metalclad

## Socket Outlets

- Complete with surface mounting box
- Top facing terminal screws
- Clear terminal markings
- Colour coded terminals
- Recessed earth bar
- Captive and backed out terminal screws
- 2 earth terminals on 2 gang sockets
- Red flagged switch indicator
- Only one size 4mm screwdriver needed
- Terminals have large lead-ins
- In compliance with BS 1363-2
- 25-year guarantee

### 13 Amp Unswitched

- M1206 1 gang unswitched
- M1208 2 gang unswitched

### 13 Amp Double Pole - Switched

- M1207DP 1 gang DP switched
- M1209DP 2 gang DP switched



M1206



M1208



M1207DP



M1209DP

#### Back Boxes

All knockouts are 20mm diameter

	Knockouts	
	sides	back
1g	5	1
2g	8	1

METALCLAD

## Plate Switches

- All plate switches are X-rated and can be used for switching inductive or fluorescent loads without de-rating
- Complete with surface mounting box
- Clear terminal markings
- Captive and backed out terminal screws
- Only one size 4mm screwdriver needed
- Terminals have large lead-ins
- In compliance with BS EN 60669-1
- 25-year guarantee

### 10 Amp

- M1203 1 gang 2-way
- M1204 2 gang 2-way
- M1205 3 gang 2-way



M1203



M1204



M1205

#### Back Boxes

All knockouts are 20mm diameter

	knockouts	
	sides	back
1g	5	1

# Metalclad

## Connection Units

- Lockable fuse carrier for safety isolation
- Captive fuse carrier
- Clear terminal markings
- Colour coded terminals
- Neon versions available
- Neon leads enclosed
- 2 earth terminals
- Captive and backed out terminals screws
- Terminals have large lead-ins
- In compliance with BS 1363: Part 4
- 25-year guarantee

### Unswitched

- M1210 13A Unswitched
- M1210FL 13A Unswitched with flex outlet
- M1217 13A Unswitched with neon

### Double Pole Switched

- M1211 13A DP switched
- M1211FL 13A DP switched with flex outlet
- M1212 13A DP switched with neon
- M1212FL 13A DP switched with flex outlet and neon



M1210



M1210FL



M1217



M1211



M1211FL



M1212



M1212FL

## Double Pole Switches

- Complete with surface mounting box
- Clear terminal markings
- Colour coded terminals
- Recessed earth bar
- Red flagged switch indicator
- Neon versions available
- Neon leads enclosed
- 2 earth terminals
- Captive and backed out terminal screws
- Terminals have large lead-ins
- In compliance with BS EN 60669-1
- 25-year guarantee

### 20 Amp

- M1213 1 gang
- M1214 1 gang with neon
- M1214FL 1 gang with flex outlet and neon

### 45 Amp

- M1300P 1 gang with neon



M1213



M1214



M1214FL



# Metalclad

## Data Plate

- Full range of data modules available, see page 35
- Accepts standard 50 x 25mm modules

M1222 Two module



M1222

## Back Boxes

- With brass earth terminal

### Knockouts

- M1228 1 gang with 6x20mm knockouts
- M1229 2 gang with 9x20mm knockouts

### No Knockouts

- M1228N 1 gang with 1x20mm knockout in rear
- M1229N 2 gang with 1x20mm knockout in rear



M1228



M1229



M1228N



M1229N

Back Boxes  
All knockouts are 20mm diameter

	knockouts	
	sides	back
1g	5	1
2g	8	1