

Lite Duty Caster Set *1425P Series*

Features



- Twin nylon swivel wheels with zinc axles and hoods.
- 5/16 - 18 threaded stem mounts into existing holes in base of rack (in place of leveling feet).
- Final mounting height of 2.75" (70 mm).
- Features zinc plated ball bearing pivot, composite wheels.

Compatibility

- RCHS/RCHV
- RCSC
- REFK
- DNRRHDW
- RS
- 1564



Part No.	Strength	Wheel Diameter	Overall Height		Caster Set		Quantity		Physical
			Added	to Cabinet	Weight	Included	Brakes	Wheel	
					Capacity	In Set	Included		Weight
1425P	Lite Duty	2.37	2.75		400	4	No		3 lb (1.4 kg)

Data subject to change without notice