



-1. Torque tools

-1.1. TORQUE TOOLS

- Torque screwdriver developed according to the scientific ERGO™ process
- Torque screwdriver, fixed setting
- Accuracy ± 10%
- Over-torque limiting clutch, with a "click" sound
- High performance alloy steel
- Chrome plated and entirely hardened. Black finish tip for higher accuracy
- Designed for correct tightening of precision fasteners, for example in CNC machines
- 6 mm hex shank
- Replaceable blades available
- Supplied with one TORX® and one TORX PLUS® blade

Ergo torque screwdriver, fixed setting

BE-6990



BE-6990-IP6	7314151846725	1	0.6	T6	55	32x113	168
BE-6990-IP7	7314151846732	1	0.9	T7	55	32x113	168
BE-6990-IP8	7314151846749	1	1.2	T8	55	32x113	168
BE-6990-IP9	7314151846756	1	1.4	T9	65	32x113	178
BE-6990-IP10	7314151846763	1	2.0	T10	65	32x113	178
BE-6990-IP15	7314151846770	1	3.0	T15	65	32x113	178

