

## KLEVA - lampholders

- complies with BS 7895
- T2 = heat resistance rating (210°C)
- automatically disconnect power at the contacts when the lamp is removed
- 50.8mm fixing centres for non-access versions. Use with mounting blocks MB326E/MT
- solid brass plungers and copper plated steel springs maintain plunger pressure throughout their long life
- body angle of angled battens set at 30°
- access lampholders have integral RL624 ceiling rose base and heat resisting PVC tails
- all lampholders incorporate automatic cord grips and sleeve caps for ease of flexible cord stripping
- home office shield encloses the lamp cap for extra safety (enabling compliance with BS 7671 in locations containing bath or shower)

<i>description</i>	<i>Pack qty.</i>	<i>cat. ref.</i>
<b>bayonet cap cord grip lampholders</b>		
KLEVA cord grip lampholders - short skirt	20	<b>SEL212</b>
KLEVA cord grip lampholders - home office shield	20	<b>SEL214</b>
<b>Straight BC batten lampholder</b>		
3 terminal, home office shield	20	<b>SEL354</b>
<b>access BC batten lampholder</b>		
straight, 2 terminal body, 3 terminal and earth base, home office shield	10	<b>SEL96T</b>
angled, 2 terminal body, 3 terminal and earth base, home office shield	10	<b>SEL106T</b>



SEL212



SEL214



SEL354



SEL96T