

Router - FL MGUARD DELTA TX/TX - 2700967

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)


Security appliance in metal housing, for desktop applications or use in the distributor room, SD card slot, intelligent firewall with full scope of functions for maximum security and ease of configuration, router with NAT/1:1 NAT, optional VPN/CIFS integrity monitoring



Why buy this product

- Maximum security
- Central management tool

Key commercial data

Packing unit	1 pc
GTIN	 4 046356 741491
Weight per Piece (excluding packing)	1000.0 g
Custom tariff number	85176200
Country of origin	Germany

Technical data

Dimensions

Width	130 mm
Height	50 mm
Depth	114 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	5 °C ... 40 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Noise immunity	EN 61000-6-2:2005

Interfaces

Interface 1	Ethernet
No. of ports	2 (RJ45)
Connection method	RJ45
Transmission physics	Ethernet in RJ45 twisted pair
Transmission speed	10/100 MBit/s

Router - FL MGUARD DELTA TX/TX - 2700967

Technical data

Interfaces

Transmission length	100 m (per segment)
Signal LEDs	Supply voltage, data transmission, error, link, activity

Function

Basic functions	Router with intelligent firewall (VPN, 10 tunnels as an option, up to 250 possible with additional license), CIFS Integrity Monitoring (as an option), metal housing, slot for SD memory card, extended temperature range, high-performance firewall/VPN (as an option): up to 99 Mbps / 35 Mbps (as an option)
Management	Web based management, SNMP or over V.24 (RS-232)
Supported browsers	HTTPS support required
Processor	330 MHz
Status and diagnostic indicators	LEDs:P1, P2, Fault, State, Error, LAN, WAN

Security functions

Dynamic Host Configuration Protocol (DHCP) support	Server or Relay Agent
Network Time Protocol (NTP) client	Client
Link Layer Discovery Protocol (LLDP)	As per protocol 802.2
Remote Syslog Logging	On external server
Virtual private network (VPN) throughput	max. 41.94304 Mbps (Router mode, VPN bidirectional throughput)
	max. 27.262976 Mbps (Stealth mode, VPN bidirectional throughput)
Number of VPN tunnels	(As an option, 10 tunnels up to 250 tunnels, Ipsec (IETF) standard with additional license FL MGUARD LIC VPN-10/ Order No. 2700194 or FL MGUARD LIC VPN-250/ Order No. 2700193 or 2700192.)
Encryption methods	DES, 3DES, AES-128, -192, -256
Firewall data throughput	max. 130.023424 Mbps (Router mode, default firewall rules, bidirectional throughput)
	max. 60.817408 Mbps (Stealth mode, default firewall rules, bidirectional throughput)
Firewall rules	Configurable stateful inspection firewall with full scope of functions
Filtering	MAC and IP addresses, ports, protocols
Protection against	IP spoofing, DoS and Syn Flood Protection
Routing	Standard routing, NAT, 1:1-NAT, port forwarding

Supply voltage

Supply voltage	230 V AC
Supply voltage range	90 V AC ... 264 V AC ((50/60 Hz))
Typical current consumption	13 mA
Max. current consumption	40 mA

General

Weight	725 g
Noise emission	EN 55022 / Class B

Router - FL MGuard DELTA TX/TX - 2700967

Classifications

eCl@ss

eCl@ss 4.0	27240409
eCl@ss 4.1	27240409
eCl@ss 5.0	27242215
eCl@ss 5.1	19030117
eCl@ss 6.0	19170106
eCl@ss 7.0	27242208
eCl@ss 8.0	27242208

ETIM

ETIM 3.0	EC001423
ETIM 4.0	EC001478
ETIM 5.0	EC001478

UNSPSC

UNSPSC 6.01	20142601
UNSPSC 7.0901	20142601
UNSPSC 11	20142601
UNSPSC 12.01	20142601
UNSPSC 13.2	20142601

Accessories

Accessories

License

License - FL MGuard LIC VPN-10 - 2700194



License for configuration and operation of 10 VPN tunnels on FL MGuard.

License - FL MGuard LIC VPN-250 - 2700193



License for configuration and operation of 250 VPN tunnels on MGuard.

Router - FL MGuard DELTA TX/TX - 2700967

Accessories

License - FL MGuard LIC LIFETIME FW - 2700184



License for lifetime software update of FL MGuard field devices.

Parameterization memory

Memory - SD FLASH 256MB - 2988120



Program and configuration memory, plug-in, 256 MB

Memory - SD FLASH 512MB - 2988146



Program and configuration memory, plug-in, 512 Mbyte.

Patch cable

Patch cable - FL CAT5 PATCH 0,3 - 2832250



Patch cable, CAT5, assembled, 0.3 m

Patch cable - FL CAT5 PATCH 0,5 - 2832263



Patch cable, CAT5, assembled, 0.5 m

Router - FL MGuard DELTA TX/TX - 2700967

Accessories

Patch cable - FL CAT5 PATCH 1,0 - 2832276



Patch cable, CAT5, assembled, 1.0 m

Patch cable - FL CAT5 PATCH 1,5 - 2832221



Patch cable, CAT5, assembled, 1.5 m

Patch cable - FL CAT5 PATCH 2,0 - 2832289



Patch cable, CAT5, assembled, 2.0 m

Patch cable - FL CAT5 PATCH 3,0 - 2832292



Patch cable, CAT5, assembled, 3.0 m

Patch cable - FL CAT5 PATCH 5,0 - 2832580



Patch cable, CAT5, assembled, 5.0 m

Router - FL MGUARD DELTA TX/TX - 2700967

Accessories

Patch cable - FL CAT5 PATCH 7,5 - 2832616



Patch cable, CAT5, assembled, 7.5 m

Patch cable - FL CAT5 PATCH 10,0 - 2832629



Patch cable, CAT5, assembled, 10.0 m

Patch cable - FL CAT6 PATCH 12,5 - 2891369



Patch cable, CAT6, pre-assembled, 12.5 m

Patch cable - FL CAT6 PATCH 15,0 - 2891372



Patch cable, CAT6, pre-assembled, 15.0 m

Patch cable - FL CAT6 PATCH 20,0 - 2891576



Patch cable, CAT6, pre-assembled, 20.0 m

Protective cap

Router - FL MGuard DELTA TX/TX - 2700967

Accessories

Dust protection - FL RJ45 PROTECT CAP - 2832991



Dust protection caps for RJ45 socket