

Snap-in markers - US-EMP (27X15) SR - 0828849

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Snap-in markers, Card, silver, Unlabeled, Can be labeled with: THERMOMARK CARD PLUS, THERMOMARK CARD, Mounting type: Snapped into marker carrier, Lettering field: 27 x 15 mm



The illustration shows a version of the product

Why buy this product

- ✓ The US-EMP ... UniSheet labeling range includes markers that can be fitted into existing CARRIER EMP ... label frames
- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- ✓ The perforated markers are easy to separate and can be easily fitted
- ✓ The sheets provide space for including function texts

Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 558525
Weight per Piece (excluding packing)	14.57 g
Custom tariff number	39204910
Country of origin	Germany

Technical data

Dimensions

Length (b)	26.9 mm
Height	0.5 mm
Width (a)	14.9 mm

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	10-25 °C / 35-65 % relative humidity. Storage in a cool and dry place is recommended.

General

Color	silver
Components	Silicone-free
Inflammability class according to UL 94	V0

Snap-in markers - US-EMP (27X15) SR - 0828849

Technical data

General

Material	PVC
	PVC
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	27
Number of individual labels per row	3
RoHS compliant	Yes
Printability	Thermal transfer
Device	5146464 THERMOMARK CARD
	5146451 THERMOMARK CARD-US-MAG1
Ink ribbon	0801371 THERMOMARK-RIBBON 110-TC
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	Following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	IEC 61010-1:2010-06
Result	Test passed
Foil strength	500 µm

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761

Snap-in markers - US-EMP (27X15) SR - 0828849

Classifications

ETIM

ETIM 5.0	EC000761
----------	----------

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Cover

Cover - CARRIER-EMP (1000X15) COVER - 0829520



Cover, transparent, Unlabeled, Mounting type: Screws, rivets, Lettering field: 1000 x 15 mm

Magazine

Magazine - THERMOMARK CARD-US-MAG1 - 5146451



Magazine for the THERMOMARK CARD printer, for accommodating US cards

Marker carriers

Marker carriers - CARRIER-EMP (1000X15) GY - 0829366



Profile, for screwing or riveting, 1000 mm long, for accommodating UC und US materials, height: 15 mm

Snap-in markers - US-EMP (27X15) SR - 0828849

Accessories

Marker carriers - CARRIER-EMP (1000X15) TR - 0829530



Marker carriers, transparent, Unlabeled, Mounting type: Screws, rivets, Lettering field: 1000 x 15 mm

Marker carriers - CARRIER/L-EMP (1000X15) GY - 0829559



Profile, self-adhesive, 1000 mm long, for accommodating UC and US materials, height: 15 mm

Marker carriers - CARRIER/L-EMP (1000X15) TR - 0829560



Marker carriers, transparent, Unlabeled, Mounting type: Adhesive, Lettering field: 1000 x 15 mm

Marker carriers - CARRIER-EMP 22 (27X15) - 0827447



Marker carriers, black, Unlabeled, Mounting type: Screws, rivets, Diameter: 22 mm, Lettering field: 27 x 15 mm

Marker carriers - CARRIER-EMLP 22 (27X15) - 0828986



Marker carriers, black, Unlabeled, Mounting type: Screws, rivets, Diameter: 22 mm, Lettering field: 27 x 15 mm

Snap-in markers - US-EMP (27X15) SR - 0828849

Accessories

Marker carriers - CARRIER-EMP (27X15) - 0827451



Marker carriers, black, Unlabeled, Mounting type: Screws, rivets, Lettering field: 27 x 15 mm