

General Information

Extended Product Type:	MCBH-11
Product ID:	1SFA611605R1111
EAN:	7320500307519
Catalog Description:	MCBH-11 CONTACT BLOCK
Long Description:	Modular contact block with holder

Categories

Products » Low Voltage Products and Systems » Control Products » Pilot Devices » Operator and Pilot Lights

Ordering

EAN:	7320500307519
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369001

Dimensions

Product Net Width:	0.048 m
Product Net Height:	0.030 m
Product Net Depth:	0.036 m
Product Net Weight:	0.032 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	0.11 m
Package Level 1 Height:	0.03 m
Package Level 1 Length:	0.15 m
Package Level 1 Gross Weight:	0.032 kg

Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
--------------	---

Additional Information

Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20
Device:	Holder for blocks incl.
IIT Publishing Status:	Level 0 - Information enabled
Illumination:	Non-illuminated
Mechanical Durability (cycles):	10 million
Number of Auxiliary Contacts NC:	1
Number of Auxiliary Contacts NO:	1
Product Main Type:	MCBH
Product Name:	CONTACT BLOCK
Product Range:	Modular
Rated Frequency (f _r):	Supply Circuit 50 Hz Supply Circuit 60 Hz
Rated Operational Current AC-15 (I _e):	(220 / 240V) 6 A (24 / 127V) 8 A
Rated Operational Current DC-13 (I _e):	(125V) 1.1 A (24V) 5 A
RoHS Date:	0635 4

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SFA1-83 ;
---------------------------------	----------------------------

Classifications

E-nummer:	3714026
ETIM 4.0:	EC002611 - Control switch
ETIM 5.0:	EC002611 - Control switch
Object Classification Code:	S
UNSPSC:	39121500