







Belegungsplan  
Loading-Plan  
acc. EIA TIA 568A  
Schirm Shield

|   |              |               |   |
|---|--------------|---------------|---|
| 1 | Weiß(grün)   | White(green)  | 1 |
| 2 | grün         | Green         | 2 |
| 3 | Weiß(orange) | White(orange) | 3 |
| 4 | Blau         | Blue          | 4 |
| 5 | Weiß(blau)   | White(blue)   | 5 |
| 6 | Orange       | Orange        | 6 |
| 7 | Weiß(braun)  | White(brown)  | 7 |
| 8 | Braun        | Brown         | 8 |



- Übertragungseigenschaften nach ISO/IEC 11801:2002: Class E.
- Schutzart: IP67/65
- Temperaturbereich: -40°C ...+70°C

- Transmission properties in accordance with ISO/IEC 11801:2002: Class E.
- Protection level: IP67/65
- Temperature range: -40°C ...+70°C



|                                       |                         |                 |
|---------------------------------------|-------------------------|-----------------|
| 8xAWG 27/7 flexibel/stranded          | 09 45 745 1553          | 20 m            |
| 8xAWG 27/7 flexibel/stranded          | 09 45 745 1551          | 10 m            |
| 8xAWG 27/7 flexibel/stranded          | 09 45 745 1527          | 5 m             |
| 8xAWG 27/7 flexibel/stranded          | 09 45 745 1525          | 3 m             |
| 8xAWG 27/7 flexibel/stranded          | 09 45 745 1523          | 1,5 m           |
| massiv / flexibel<br>solid / stranded | Bestell-Nr.<br>Part-No. | Maß a<br>Dim. a |

| All Dimensions in mm<br>Original Size DIN A 3 |          |      | Techn. Character. |          |      | Nicht tolerierte Maß/Free size Tolerances              |                                                                                                                           |             |
|-----------------------------------------------|----------|------|-------------------|----------|------|--------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------|-------------|
|                                               |          |      |                   | Dat.     | Name | Maßstab/Scale<br><br>2:1                               | RJ45 Kabel 8xAWG 27/7, Class E, flexibel,<br>RJ45 cable 8xAWG 27/7, Class E, stranded,<br>4x2x0,09 2xRJ45, IP67 Push Pull |             |
|                                               |          |      | Detail.           | 25.06.04 | Wie  |                                                        |                                                                                                                           |             |
|                                               |          |      | Insp.             | 25.06.04 | Wae  |                                                        |                                                                                                                           |             |
|                                               |          |      | Stand.            |          |      |                                                        |                                                                                                                           |             |
| 32405                                         | 10.11.04 | Wie  |                   |          |      | HARTING Electronics GmbH & Co. KG<br>D-32339 ESPELKAMP | TB 09 45 745 1523                                                                                                         |             |
| 32192                                         | 16.08.04 | Wie  |                   |          |      |                                                        |                                                                                                                           |             |
| 32073                                         |          |      |                   |          |      |                                                        |                                                                                                                           |             |
| Mod.                                          | Dat.     | Name |                   |          |      |                                                        | Sub.                                                                                                                      | Blatt/ page |

