

Number of contacts

2x4



Identification	Part-Number		Drawings	Dimensions in mm
	Male insert (M)	Female insert (F)		
Module 	09 14 001 3011	09 14 001 3111		

Han Modular

Identification	Wire gauge mm ²	Part-Number		Drawings	Dimensions in mm
		Male contacts (M)	Female contacts (F)		
Han® MegaBit insert 2 x 4 contacts crimp contacts order separately		09 14 008 3016	09 14 008 3116		Contact arrangement View termination side
2 x 4 contacts with additional shield connection to the hinged frame crimp contacts order separately		09 14 008 3017	09 14 008 3117		

Identification	Wire gauge mm ²	Part-Number		Drawings
		Male contacts (M)	Female contacts (F)	
Han D® crimp contacts gold plated 	0.14-0.37 0.5 0.75 1.0 1.5 2.5	09 15 000 6124 09 15 000 6123 09 15 000 6125 09 15 000 6122 09 15 000 6121 09 15 000 6126	09 15 000 6224 09 15 000 6223 09 15 000 6225 09 15 000 6222 09 15 000 6221 09 15 000 6226	

Wire gauge		∅	Stripping length of stranded wire
0.14 - 0.37 mm ²	AWG 26-22	0.9	8 mm
0.5 mm ²	AWG 20	1.1	8 mm
0.75 mm ²	AWG 18	1.3	8 mm
1.0 mm ²	AWG 18	1.45	8 mm
1.5 mm ²	AWG 16	1.75	8 mm
2.5 mm ²	AWG 14	2.25	6 mm

06
95

Stock items in bold type