





NOTE:

1. MAXIMUM ELECTRIC CURRENT :

A.W.G.	16	14	
AMP.	10	15	
2. MAXIMUM ELECTRICAL RATING : 125°C 300 VOLTS MAX.
3. INSULATION MATERIAL : PC
4. INSULATION COLOR : BLUE
5. TERMINAL MATERIAL : BRASS
6. WIRE RANGE : 16-14 A.W.G.(1.5-2.5 mm²)
7. TERMINALS SURFACE TREATMENT : TIN PLATED
8. THICKNESS : 0.40 mm
9. NEMA TAB : 0.032*0.250 (0.8 * 6.35)

Tolerance Unless Otherwise Specified			
0 > 6	mm ± 0.20	ANGLE	
6 > 18	mm ± 0.30	0° >	° REF ±
18 > 30	mm ± 0.40	° >	° ±
30 > 75	mm ± 0.50	° >	° ±

NAME	PC-INSULATED FEMALE DISCONNECTORS			UNIT	mm	
PART NO.	FDNI2-250@	MATERIAL	-----	APPROVE	3年乙巨	
NUMBER	KA-95844-C	SCALE	SHEET	PAGE	CHECKED	楊駿海
DATE	2006/07/20	4/1	1-0	20F2	DRAWN	張馨尹

