

DIGITAL CAMERA		PowerShot SX710 HS
IMAGE SENSOR		
	Type	1/2.3 type back-illuminated CMOS
	Effective Pixels	Approx. 20.3M [14]
	Colour Filter Type	Primary Colour
IMAGE PROCESSOR		
	Type	DIGIC 6 with iAPDS technology
LENS		
	Focal Length	4.5 – 135.0 mm (35 mm equivalent: 25 – 750 mm)
	Zoom	Optical 30x ZoomPlus 60x Digital Approx. 4.0x (with Digital Tele-Converter Approx. 1.6x or 2.0x [1]) Combined Approx. 120x
	Maximum f/number	f/3.2 – f/6.9
	Construction	13 elements in 10 groups (3 UD lenses, 2 double-sided aspherical lenses)
	Image Stabilisation	Yes (lens shift-type), Approx. 2.5-stop [13]. Intelligent IS plus 5-axis Advanced Dynamic IS
FOCUSING		
	Type	TTL
	AF System/ Points	AiAF (Face Detection / 9-point), 1-point AF (fixed to centre)
	AF Modes	Single, Continuous, Servo AF/AE [6], Tracking AF,
	AF Point Selection	Size (Normal, Small)
	AF Lock	Yes
	AF Assist Beam	Yes
	Manual Focus	Yes, plus MF Peaking
	Closest Focusing Distance	1 cm (W) from front of lens in Macro
EXPOSURE CONTROL		
	Metering modes	Evaluative (linked to Face Detection AF frame), Centre-weighted average, Spot (Centre)
	AE Lock	Yes
	Exposure Compensation	+/- 2 EV in 1/3 stop increments. Enhanced i-Contrast for automatic dynamic range correction
	ISO sensitivity	AUTO, 100, 200, 400, 800, 1600, 3200
SHUTTER		
	Speed	1 – 1/3200 sec. (factory default) 15 – 1/3200 sec. (total range – varies by shooting mode)
WHITE BALANCE		
	Type	TTL
	Settings	Auto (including Face Detection WB), Daylight, Cloudy, Tungsten, Fluorescent, Fluorescent H, Custom. Multi-area WB correction available in Smart Auto
COLOUR MATRIX		
	Type	sRGB
LCD MONITOR		
	Monitor	7.5 cm (3.0") sRGB PureColor II G LCD (TFT). Approx. 922,000 dots
	Coverage	Approx. 100%
	Brightness	Adjustable to one of five levels. Quick-bright LCD

FLASH		
	Modes	Auto, Manual Flash On / Off, Slow Synchro
	Slow Sync Speed	Yes. Fastest speed 1/2000 sec.
	Red-Eye Reduction	Yes
	Flash Exposure Compensation	+/- 2 EV in 1/3 stop increments. Face Detection FE, Safety FE, Smart Flash Exposure
	Flash Exposure Lock	Yes
	Manual Power Adjustment	3 levels with internal flash
	Built-in Flash Range	50 cm – 3.5 m (W) / 1.4 m – 2.0 m (T)
SHOOTING		
	Modes	Smart Auto (58 scenes detected), Hybrid Auto, Creative Shot, Program AE, Shutter priority AE, Aperture priority AE, Manual, Live View Control, Sports, SCN (Portrait, Smart Shutter (Smile, Wink Self-Timer, FaceSelf-Timer), Handheld Night Scene, Low Light (5.0 MP), Snow, Fireworks), Creative Filters (Fish-eye Effect, Miniature Effect, Toy Camera Effect, Monochrome, Soft Focus, Super Vivid, Poster Effect), Movie
	Modes in Movie	Smart Auto (21 scenes detected), Standard, Program AE, Portrait, Miniature Effect, Monochrome, Super Vivid, Poster Effect, Snow, Fireworks, Short Clip, iFrame Movie
	Photo Effects	My Colors (My Colors Off, Vivid, Neutral, Sepia, Black & White, Positive Film, Lighter Skin Tone, Darker Skin Tone, Vivid Blue, Vivid Green, Vivid Red)
	Drive modes	Single, Auto Drive, Continuous, Continuous with AF, Self-Timer
	Continuous Shooting	Approx. 6.0 shots/sec until memory card becomes full [12] with AF: Approx. 4.5 shots/sec [3][4] with Live View: Approx. 4.5 shots/sec [3][4]
RECORDING PIXELS / COMPRESSION		
	Image Size	4:3 - (L) 5184 x 3888, (M1) 3648 x 2736, (M2) 2048 x 1536, (S) 640 x 480 16:9 - (L) 5184 x 2912, (M1) 3648 x 2048, (M2) 1920 x 1080, (S) 640 x 360 3:2 - (L) 5184 x 3456, (M1) 3648 x 2432, (M2) 2048 x 1368, (S) 640 x 424 1:1 - (L) 3888 x 3888, (M1) 2736 x 2736, (M2) 1536 x 1536, (S) 480 x 480
	Compression	Resize in playback (M2) Superfine, Fine
	Movies	(Full HD) 1920 x 1080, 60/30 fps, (HD) 1280 x 720, 30 fps, (L) 640 x 480, 30 fps
	Movie Length	Miniature Effect (HD, L) 6 fps, 3 fps, 1.5 fps Hybrid Auto Movie (HD) 30 fps iFrame Movie (Full HD) 30 fps Short Clip (HD) 30 fps (Full HD & HD) Up to 4 GB or 29 min. 59 sec. [7] (L) Up to 4 GB or 1 hour [4]
FILE TYPES		
	Still Image Type	JPEG compression, (Exif 2.3 [Exif Print] compliant) / Design rule for Camera File system, Digital Print Order Format [DPOF] Version 1.1 compliant
	Movies	MP4 [Video: MPEG-4 AVC / H.264, Audio: MPEG-4 AAC-LC (stereo)]

DIRECT PRINT		
	Canon Printers	Canon SELPHY Compact Photo Printers and Canon Inkjet Printers supporting PictBridge
	PictBridge	Yes (via USB or Wireless LAN)
OTHER FEATURES		
	GPS	GPS via mobile (linked to compatible smartphone)
	Red-Eye Correction	Yes, during shooting and playback
	Intelligent Orientation Sensor	Yes, with Auto Rotate
	Histogram	Yes
	Playback zoom	Approx. 2x – 10x
	Self Timer	Approx. 2 or 10 sec. or Custom
	Menu Languages	English, German, French, Dutch, Danish, Finnish, Italian, Greek, Norwegian, Portuguese, Russian, Swedish, Spanish, Ukrainian, Polish, Czech, Hungarian, Turkish, Simplified Chinese, Chinese (traditional), Japanese, Korean, Thai, Arabic, Romanian, Farsi, Hindi, Malay, Indonesian, Vietnamese, Hebrew
INTERFACE		
	Computer	Hi-Speed USB (MTP, PTP) dedicated connector (Mini-B compatible)
	Other	HDMI Micro Connector, A/V output (PAL/NTSC)
	Computer/Other	Wi-Fi (IEEE802.11b/g/n), (2.4 GHz only), with Dynamic NFC support [11]
MEMORY CARD		
	Type	SD, SDHC, SDXC
SUPPORTED OPERATING SYSTEM		
	PC & Macintosh	Windows 8 / 8.1 / 7 SP1 Mac OS X 10.8 / 10.9
		For Wi-Fi connection to a PC: Windows 8 / 8.1 / 7 SP1 only Mac OS X 10.8.2 or later / 10.9
SOFTWARE		
	Other	CameraWindow DC Map Utility Image Transfer Utility
POWER SOURCE		
	Batteries	Rechargeable Li-ion Battery NB-6LH (battery and charger supplied)
	Battery life	Approx. 230 shots Eco mode: 315 shots
	A/C Power Supply	Approx. 240 min. playback Optional, AC Adapter Kit ACK-DC40
ACCESSORIES		
	Cases / Straps	Soft Case DCC-1570 Travel Case DCC-2500 PowerShot Accessory Organizer
	Power Supply & Battery Chargers	AC Adapter Kit ACK-DC40 Battery Charger CB-2LYE
	Other	Canon AV cable AVC-DC400ST Interface Cable IFC-400PCU

PHYSICAL SPECIFICATIONS		
	Operating Environment	0 – 40 °C, 10 – 90% humidity
	Dimensions (WxHxD)	112.7 x 65.8 x 34.8 mm
	Weight	Approx. 269 g (including battery and memory card)
All data is based on Canon standard testing methods (according to CIPA Standards) except where indicated. Subject to change without notice. [1] Depending on the image size selected. [3] Under conditions where the flash does not fire. [4] Depending on memory card speed / capacity / compression setting. [6] Some settings limit availability. [7] The following Speed Class memory cards are required for maximum record time: (HD) 1280 x 720 Speed Class 4 or above. (Full HD) 1920 x 1080 Speed Class 6 or above. (iFrame) 1280 x 720 Speed Class 6 or above. [11] Wi-Fi use may be restricted in certain countries or regions. Wi-Fi support varies by device and region. For more information visit www.canon-europe.com/wirelesscompacts [13] Values at maximum optical focal length. Cameras whose focal length exceeds 350 mm (35 mm equivalent) are measured at 350 mm. [14] Image processing may cause a decrease in the number of pixels.		