

Thrust ball bearings, single direction



Principal dimensions			Basic load ratings		Fatigue load limit	Minimum load factor	Speed ratings		Mass	Designation
d	D	H	dynamic	static	P_u	A	Reference speed	Limiting speed		
mm			kN	C_0	kN	-	r/min		kg	-
20	35	10	15,1	29	1,08	0,0044	7500	10000	0,039	51104

