




NOTES:

- ATTENUATION $\leq 0,30$ dB, MEASURED AT 1300nm ACC. TO IEC 874-1
CLAUSE 4.4.7 METHOD 7 EQUILIBRIUM MODE CONDITION.
- FILLED OUT TEST RESULT SHEET WILL BE SUPPLIED WITH EACH INDIVIDUALLY
PACKED ASSEMBLY.

- 3** BLANK LABEL.
- 4** CABLE LABEL INFO:
- UNIQUE SERIAL NUMBER
 - TYCO LOGO PN
 - MANUFACTURING LOCN.

- 5** REEL LABEL INFO:
- TYCO LOGO, MFG LOCATION
 - DESCRIPTION
 - TYCO PART NUMBER, REV
 - BARCODE

- 6** NON CROSS OVER AS PER TABLE.
- 7** CABLE LENGTHS MORE THAN 40m WILL BE SUPPLIED ON REEL.

8. CABLE INFO:
- CORE DIA — 62.5/125 μ m
 - OUTER DIAMETER — 2,5 x 5,0 mm
 - JACKET COLOR — ORANGE
 - JACKET MAYERIAL — LSZH

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-5349580-Y	XY,0

1	—	FOPK BOX	—
1	—	FOPK REEL 7	—
1	—	FOAC REEL LABEL 5	—
2	—	DAT-85 LABEL	12
2	—	KIT, MM, CER, ASSY, BULK	11
2	—	ST CRIMP EYELET	10
1	—	ST BOOT RED	9
1	—	ST BOOT BLACK	8
4	—	DUST CAP, BLACK	7
1	—	SC DUPLEX HOUSING, BEAM HALF	6
1	—	SC DUPLEX HOUSING, RET. PLATE HALF	5
2	—	SC CERAMIC, OVERMOLDED	4
2	—	SC CRIMP EYELET	3
2	—	SC BOOT, BEIGE	2
L	—	FOCAB 62,5/125TZ 2.5S ORANGE	1
Qty	Part Number	Description	Item
THIS DRAWING IS A CONTROLLED DOCUMENT.			
DWN 12 SEP 05 CHK 12 SEP 05 APVD 12 SEP 05		GIRIYAPPA M DIWAKAR BELAVADI DIWAKAR BELAVADI	
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH	
MATERIAL		WEIGHT	
—		—	
CUSTOMER DRAWING		SCALE NTS	
SHEET 1 OF 1		REV A	

tyco

Electronics

Tyco Electronics Corporation
FOBU, Bangalore, India

NAME

FOMM62.5 LEAD 2,5S TZ SC - ST DPX

SIZE A2

CAGE CODE 00779

DRAWING NO C=5349580

RESTRICTED TO