

SHIPPING SPECIFICATIONS FOR GLASS FIBRE PRODUCTS

LADDERS:-- STILES 84 x 30 x 3mm Channel  
 RUNGS Alloy 30mm dia 4.5mm WALL incl 2.25mm Serration  
 Rungs Glass Fibre 30 x 30 x 3.5mm incl 1mm Serration

SINGLE SECTION length x 415mm wide x 84mm deep  
 TWO SECTION length x 415mm wide x 165mm deep  
 THREE SECTION length x 415mm wide x 245mm deep

ROPE OPERATED LADDERS over all width is 440mm

STEPS :- STILES 84 x 30 x 3mm Channel  
 BACK FRAME and BRACES 45 x 35 x 3mm Channel  
 TREAD ALLOY 81 x 31 x 2.5mm Serrated Channel 67 degree  
 TREAD GLASS FIBRE 84 x 32 x 3.5mm Serrated Channel 68 degree

CODE NUMBER PLATFORM	O/ALL LENGTH mt	HT/OPEN PLT mt	TOP WIDTH mm	BOTTM WIDTH mm	DEPTH mm	BASE SPAN mm	APPROX WEIGHT kg
GSP & AFPS04	1.53	0.93	375	475	160	1130	9.5
GSP & AFPS05	1.78	1.18	375	500	160	1300	11.0
GSP & AFSP06	2.03	1.43	375	525	160	1470	12.5
GSP & AFSP07	2.29	1.68	375	550	160	1640	14.5
GSP & AFSP08	2.54	1.93	375	575	160	1810	16.5
GSP & AFSP09	2.80	2.18	375	600	160	1980	19.0
GSP & AFSP10	3.05	2.43	375	625	160	2150	21.5
SWINGBACK							
GSB & AFSB04	1.02		335	425	160	790	7.0
GSB & AFSB05	1.25		335	450	160	960	8.0
GSB & AFSB06	1.53		335	475	160	1130	9.5
GSB & AFSB07	1.78		335	500	160	1300	11.0
GSB & AFSB08	2.03		335	525	160	1470	12.5
GSB & AFSB09	2.29		335	550	160	1640	14.0
GSB & AFSB10	2.54		335	575	160	1810	16.5
DOUBLE SIDE							
GTS & AFDS04	1.09	0.94	380	430	180	965	12.0
GTS & AFDS05	1.35	1.17	380	455	180	1170	13.0
GTS & AFDS06	1.60	1.45	380	480	180	1400	14.5
GTS & AFDS07	1.85	1.64	380	505	180	1560	16.0
GTS & AFDS08	2.11	1.87	380	530	180	1755	17.5
GTS & AFDS09	2.36	2.11	380	555	180	1945	19.5
GTS & AFDS10	2.62	2.34	380	580	180	2135	22.0