


NO	DESCRIPTION	DATE
△	RUBBER — SILICONE	09.09.09
△	NICKEL 100μ <sup>2</sup> MIN. — NICKEL	04.13.11



### 1.0 ELECTRICAL

- 1.1 FREQUENCY RANGE: DC-3 GHz
- 1.2 NOMINAL IMPEDANCE: 50 OHMS
- 1.3 WORKING VOLTAGE: 500 VOLTS MAX.
- 1.4 PROOF VOLTAGE: 1000 VOLTS
- 1.5 VSWR: 1.3 MAX.

### 2.0 MATERIALS

- 2.1 BODIES: BRASS PER JIS-C3604
- 2.2 CENTER CONTACT: BRASS PER JIS-C3604
- 2.3 INSULATION: TEFLON PER ASTM D1457 AND ASTM D1710

### 3.0 FINISHES AND OTHERS

- 3.1 SEE BELOW TABLE FOR DETAILS.

### 4.0 ENVIRONMENTAL

- 4.1 OPERATING TEMPERATURE RANGE: -40° C TO +85° C

NO	DESCRIPTION	MATERIAL	Q'TY	FINISH
9	INSULATION	TEFLON	1	NONE
8	CENTER CONTACT	BRASS	1	GOLD
7	BODY	BRASS	1	NICKEL 100μ <sup>2</sup> MIN.
6	WASHER	BRASS	1	NICKEL
5	SPRING WASHER	SK-5	1	NICKEL
4	WASHER	BRASS	1	NICKEL
3	GASKET	SILICONE	1	RED
2	INSULATION	TEFLON	1	NONE
1	SHELL	ZINC	1	NICKEL

APPROVED by \_\_\_\_\_ DATE: \_\_\_\_\_



DESCRIPTION		BNC PLUG - F JACK ADAPTER		DATE		REV.	
製	DRAWN	TOLERANCE	品名	13-47-3	T.G.Z	日期	01.06.09
圖	Yoko	.X ±0.2	TITLE	\ROHS COMPLIANT (750)		版次	A-2
檢	CHECK	.XX ±0.1	單位	DWG.NO.	13-0162		
定	Arc	.XXX ±0.05	SCALE				
	APPROVAL	ANGLE ±5°	比例				
	Jenny						