

## PAR 30

Wattage [W]	Colour	Length [mm]	Product Description	CCT [K]	CRI [Ra]	Initial Lumen [lm] (candela [cd])	Cap	Rated avg. life horizontal [h]	Rated avg. life vertical [h]	Pack qty.	Product Code
20	WDL	124	CMH20PAR30/UVC/830/E27/SP10	3000	80+	1200 (19800)	E27	12,000	12,000	6	26497
20	WDL	124	CMH20PAR30/UVC/830/E27/FL25	3000	80+	1200 (4900)	E27	12,000	12,000	6	26518
35	WDL	124	CMH35/PAR30/UVC/830/E27/SP10	3000	80+	2400 (39600)	E27	10,000	10,000	6	21689
35	WDL	124	CMH35/PAR30/UVC/830/E27/FL25	3000	80+	2400 (11000)	E27	10,000	10,000	6	21690
35	NDL	124	CMH35/PAR30/UVC/942/E27/SP10	4200	89	2225 (36700)	E27	10,000	10,000	6	44939
35	NDL	124	CMH35/PAR30/UVC/942/E27/FL25	4200	89	2225 (10200)	E27	10,000	10,000	6	44942
70	WDL	124	CMH70/PAR30/UVC/830/E27/SP15	3000	80+	4700 (43000)	E27	13,000	13,000	6	21683
70	WDL	124	CMH70/PAR30/UVC/830/E27/FL40	3000	80+	4700 (10000)	E27	13,000	13,000	6	21682
70	NDL	124	CMH70/PAR30/UVC/942/E27/SP15	4200	89	4300 (33500)	E27	10,000	10,000	6	74620
70	NDL	124	CMH70/PAR30/UVC/942/E27/FL40	4200	89	4300 (9000)	E27	10,000	10,000	6	74619



## Elliptical Clear

Wattage [W]	Colour	Length [mm]	Product Description	CCT [K]	CRI [Ra]	Initial Lumen [lm]	Cap	Rated avg. life horizontal [h]	Rated avg. life vertical [h]	Pack qty.	Product Code
70	WDL	137	CMH70/E/UVC/U/830/E27/C	3000	80+	6300	E27	15,000	15,000	6	46189
100	WDL	137	CMH100/E/UVC/U/830/E27/C	3000	80+	9200	E27	15,000	15,000	6	46191
150	NDL	137	CMH150/UVC/O/U/942/E27/C	4200	90	13200	E27	15,000	15,000	6	43285



## Elliptical Diffuse

Wattage [W]	Colour	Length [mm]	Product Description	CCT [K]	CRI [Ra]	Initial Lumen [lm]	Cap	Rated avg. life horizontal [h]	Rated avg. life vertical [h]	Pack qty.	Product Code
70	WDL	137	CMH70/E/UVC/U/830/E27/D	3000	80+	6000	E27	15,000	15,000	6	46187
70	NDL	137	CMH70/UVC/O/U/940/E27/D	4000	90	5300	E27	15,000	15,000	6	43282
100	WDL	137	CMH100/E/UVC/U/830/E27/D	3000	80+	8700	E27	10,000	10,000	6	46194
150	NDL	137	CMH150/UVC/O/U/940/E27/D	4000	90	12300	E27	15,000	15,000	6	43286
250	WDL	251	CMH250/E/UVC/U/830/E40/D	3000	80+	23500	E40	24,000	24,000	6	10591
400	WDL	280	CMH400/E/UVC/U/830/E40/D	3000/3600	80+	39000	E40	20,000	20,000	6	13087



## Tubular Clear

Wattage [W]	Colour	Length [mm]	Product Description	CCT [K]	CRI [Ra]	Initial Lumen [lm]	Cap	Rated avg. life horizontal [h]	Rated avg. life vertical [h]	Pack qty.	Product Code
70	WDL	156	CMH70/TT/UVC/830/E27	3000	80+	6400	E27	20,000	15,000	12	38752
100	WDL	207	CMH100/TT/UVC/830/E40	3000	80+	9200	E40	15,000	10,000	12	92478
150	WDL	207	CMH150/TT/UVC/830/E40	3000	80+	14000	E40	20,000	15,000	12	38749
150	NDL	207	CMH150/UVC/T/U/842/E40	4000	89	14500	E40	15,000	15,000	12	21514
150	WDL	207	CMH150/UVC O/T/U/830/E40	3000	80+	14000	E40	12,000	12,000	12	21516
150	NDL	207	CMH150/UVC O/T/U/942/E40	4200	90+	14000	E40	15,000	15,000	12	21517
250	WDL	251	KRC250/CMH/830/T/H/E40	3000	80+	20000	E40	24,000	N/A	12	20302
250	WDL	251	CMH250/TT/UVC/U/830/E40	3000	80+	25000	E40	24,000	24,000	12	10589
250	NDL	260	CMH250/T/U/942/E40	4200	80+	25000	E40	16,000*	16,000*	12	62356
400	WDL	270	CMH400/TT/UVC/U/830/E40	3000/3600	80+	41000	E40	20,000	20,000	12	13067

\*Testing continuous to establish final design life



## Tubular Clear StreetWise™

Wattage [W]	Colour	Length [mm]	Product Description	CCT [K]	CRI [Ra]	Initial Lumen [lm]	Cap	Rated avg. life horizontal [h]	Rated avg. life vertical [h]	Pack qty.	Product Code
50	WDL	156	CMH50/TT/UVC/730/E27/ECG STREETWISE	3000	70+	5000	E27	24,000	N/A	12	64982
50	WDL	156	CMH50/TT/UVC/730/E27/EM STREETWISE	3400	67	4500	E27	24,000	N/A	12	77400
70	WDL	156	CMH70/TT/UVC/730/E27 STREETWISE	3000	70+	7640	E27	24,000	N/A	12	77401
100	WDL	211	CMH100/TT/UVC/730/E40 STREETWISE	3000	70+	10900	E40	24,000	N/A	12	77399
150	WDL	211	CMH150/TT/UVC/730/E40 STREETWISE	3000	70+	16300	E40	24,000	N/A	12	77402



## Electronic HID Ballast - Miniature

Wattage [W]	Line Voltage [V]	Product Description	Type	Pack qty.	Product Code
20	220-240	BLS/E/20W/CMH 220-240V	Integral	12	78711
20	220-240	BLS/E/20W/CMH /R CC 220-240V	Remote	12	78712
20	220-240	BLS/E/20W/CMH /R LP 220-240V	Remote with plug	12	78713
35	220-240	BLS/E/35W/CMH 220-240V	Integral	12	78714
35	220-240	BLS/E/35W/CMH/R CC 220-240V	Remote	12	78715
35	220-240	BLS/E/35W/CMH/R LP 220-240V	Remote with plug	12	78716



## Electronic HID Ballast - Standard

Wattage [W]	Line Voltage [V]	Product Description	Type	Pack qty.	Product Code
35	220-240	BLS/E/35W/CMH 220-240V ECO	Integral	10	61487
35	220-240	BLS/E/35W/CMH /R CC 220-240V ECO	Remote	10	61488
70	220-240	BLS/E/70W/CMH	Integral	10	61376
70	220-240	BLS/E/70W/CMH/R CC	Remote	10	61569

