

**MS19**  
**Insulated T-handled hexagonal box spanner**

**Normes :**

**Usage :**

can take a rod throughout its length, for rapid tightening of nuts difficult of access.



REFERENCES AVAILABLE	Length (mm)	Ø (mm)	Weight (g)
<b>MS19 19HT700</b>	700 (12 sided)	19	1900
<b>MS19 21HT700</b>	700 (12 sided)	21	1900
<b>MS19 13HT405</b>	405	13	650
<b>MS19 14HT405</b>	405	14	800
<b>MS19 17HT405</b>	405	17	900
<b>MS19 19HT405</b>	405	19	1000
<b>MS19 21HT405</b>	405	21	1200
<b>MS19 10HT305</b>	305	10	350
<b>MS19 11HT305</b>	305	11	360
<b>MS19 12HT305</b>	305	12	370
<b>MS19 13HT305</b>	305	13	400
<b>MS19 14HT305</b>	305	14	450
<b>MS19 16HT305</b>	305	16	560
<b>MS19 17HT305</b>	305	17	650
<b>MS19 19HT305</b>	305	19	750
<b>MS19 21HT305</b>	305	21	800
<b>MS19 22HT305</b>	305	22	850
<b>MS19 23HT305</b>	305	23	900
<b>MS19 24HT305</b>	305	24	940