

MNX PCM 100/125 G



Sample photo

Order symbol: PCM 100/125 G
Product nbr: 6016304
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074038029
El. number:
 Finland: 3421633
 Electric No. Denmark: 8212027048
 Electric No. Italy: 7341020
 Electric No. Sweden: 2535309

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	130	80	125	MIN 5	DIN-15 Mounting rail
inch:	5.1	3.1	4.9	MIN 10	DIN-15 Mounting rail
Materials:				MIV 5	DIN-35 Mounting rail
Material:	Polycarbonate			MIV 10	DIN-35 Mounting rail
Base colour:	RAL 7035 -light grey			FP A 100/130	Front plate (Aluminium)
Cover screws material:	Polyamide			HFP 130	Front plate hinge series
Cover colour:	RAL 7035 -light grey			FP 22046	Wall fastening lug (4 pcs)
Cover screws colour:	Grey			Rating:	
Gasket material:	TPE			Ingress Protection (EN 60529): IP66/IP67	
Temperatures:				Impact Resistance (EN 62262): IK08	
Temperature °C (short term):	-40 ... 120 °C			Electrical insulation: Totally insulated	
Temperature °C (continuous):	-40 ... 80 °C			Halogen free (DIN/VDE 0472, Part 815): 1	
Temperature °F (short term):	-40 ... 250 °F			UV resistance: UL 508	
Temperature °F (continuous):	-40 ... 175 °F			Flammability Rating: UL 746C 5V	
Accessories:				Glow Wire Test (IEC 695-2-1) °C: 960	
MIV 100	Mounting plate (Galvanized steel)			NEMA Class: NEMA 1, 4, 4X, 6	
				Certificates:	
				Germanischer Lloyd (GL)	
				SGS Fimko	
				Gost R	

