



iM2500

Medium Case

Travel Case



Two Press & Pull Latches

- Two Press & Pull Latches
- Double-layered, Soft-grip Handle
- Two Padlockable Hasps
- In-line Wheels
- Telescoping Handle
- Vortex® Valve
- Flush Powerful Hinges
- Meets airline regulations for carry-on luggage*
- Lightweight Strong HPX® Resin
- Watertight
- Check with your airline for exact measurement requirements
- *Check with your airline for exact measurement requirements
- Peli's limited lifetime guarantee**
- Peli's limited lifetime guarantee****Where applicable by law
- **Where applicable by law

CONFIGURATIONS

iM2500 - Standard

iM2500-X0000 - With No Foam

iM2500-X0002 - With With Padded Dividers

DIMENSIONS

Interior (L x W x D): 20.50 x 11.50" x 7.20 (52.1 x 29.2 x 18.3 cm)

Exterior (L x W x D): 21.70 x 14.10" x 8.90 (55.1 x 35.8 x 22.6 cm)

Lid Depth: 2.00"

Bottom Depth: 5.20"

Total Depth: 7.2"

Int Volume: 0.98 ft³

MATERIALS

Body: Injection Molded HPX® high performance resin

Latch: Valox - Polybutylene Terephthalate (PBT)

Latch (Alt): Xenoy - Polyester/Polycarbonate blend

O-Ring: Silicone Sponge

Pins: Stainless Steel

Pins (Alt): Aluminum

Foam: 1.3/1.35 polyester

Purge Body: Valox - Polybutylene Terephthalate (PBT)

Purge Body (Alt): Xenoy - Polyester/Polycarbonate blend

Purge Vent: Gortex membrane

Purge O-Ring: Buna-N, 50-60 Durometer Shore A

COLOURS



Black



Yellow



OD Green

WEIGHT

Weight With Foam: 13.70 lbs

Weight Without Foam: 11.10 lbs

Buoyancy: 62.56 lbs

Master Pack Weight: 42.10 lbs

TEMPERATURE

Minimum Temperature: -20°

Maximum Temperature: 140°

CERTIFICATIONS

MIL-STD-810F

ATA 300

FED-STD-101C

FOAM PROPERTIES

Layer 1 (Lid): 2.00" Convolute

Layer 2 (Base): 0.50" Pad

Layer 3 (Base): 1.62" Pick N Pluck

Layer 4 (Base): 1.62" Pick N Pluck

Layer 5 (Base): 1.62" Pick N Pluck

OTHER

Extendable Handle: yes

Master Pack: 3

Military: yes

Peli Products, S.L.U.

c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999

info@peli.com • www.peli.com