






	PER DETAIL E		4.32	[.170]	1-5747299-6
	PER DETAIL E		3.18	[.125]	1-5747299-4
OBSOLETE	PER DETAIL E		3.18	[.125]	1-5747299-3
	PER DETAIL D		3.18	[.125]	5747299-8
			3.18	[.125]	5747299-7
	AS SHOWN		4.32	[.170]	5747299-4
			3.18	[.125]	5747299-2
	HARDWARE OPTIONS	CONTACTS	C		PART NO
		FINISH			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN B. LATUCCA 22SEP2005 ORK S. BOLASH 22SEP2005		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± - 1. PLC ± - 2. PLC ± 0.13 [0.005] 3. PLC ± - 14. PL ± - ANGLES ± -		NAME RECEPTACLE ASSEMBLY, SIZE 2, 15 POSITION, FRONT METAL SHELL, WITH OR WITHOUT SCREWLOCKS OR INSERTS, AMPLIMITE HO-20	
		APVD M. WALMSLEY 22SEP2005 PRODUCT SPEC 108-40025 APPLICATION SPEC 114-40023		SIZE A1	
MATERIAL 		FINISH 		CAGE CODE 00779	
		WEIGHT -		DRAWING NO C-5747299	
		CUSTOMER DRAWING		RESTRICTED TO -	
				SCALE 4:1	
				SHEET 1 of 1	
				REV B	