

CASES
1060
Micro Case

Save as PDF



Peli protector cases - Total protection boxes - Crushproof case - 1060 Micro Case



Interior dimensions:
 20.9 x 10.8 x 5.7 cm (8" x 4" x 2")

GREAT FOR RUGGED SPORTS - NOT FOR SWIMMING OR SUBMERGING

Water resistant, crushproof, and dust proof. Not for swimming or diving.

Easy open latch

Rubber liner for extra protection doubles as o-ring seal

Automatic Pressure Equalization Valve - balances interior pressure, keeps water out

Stainless steel hardware

Lanyard

Unconditionally Guaranteed

Available in solid colour or clear with coloured liner



Micro_black Micro_blue Micro_red Micro_yellow

Peli protector cases - Total protection boxes - Crushproof case - 1060 Micro Case SPECIFICATIONS

Exterior Dimensions (L x W x D)		Interior Dimensions (L x W x D)	
23.8 x 14.1 x 6.7 cm (9" x 6" x 3")		20.9 x 10.8 x 5.7 cm (8" x 4" x 2")	
Lid Depth	Bottom Depth	Total Depth	
1.8 cm (1")	3.7 cm (1.44")	5.4 cm (2.13")	
Lid Depth	Bottom Depth	Total Depth	
1.8 cm (0.69")	3.7 cm (1.44")	5.4 cm (2.13")	
Weight w/Foam	Weight w/o Foam	Buoyancy Max.	
0.47 kg. (1.03 lbs)	0.45kg (1 lbs.)	1.13 kg (2.49 lbs.)	
Range Temperature			
-23 / 93° C (-10 / 199.4° F)			

1060 Micro Case Certificates

- IP67(1 meter submersion for 30 minutes)

Materials

Body	Latch	Lid O-Ring	Pins
Polycarbonate	Xylex	Thermal Plastic Rubber Liner Stainless Steel	
Foam	Purge Body	Purge Vent	Purge O-Ring
TL - 426 4 lb. Esther	Polycarbonate	Polyester Spun- Bond ePTFE Oleophobic	70 Shore Nitrile

Configuration

Cat. #	Description
1060	Peli protector cases - Total protection boxes - Crushproof case - 1060 Micro Case

Peli protector cases - Total protection boxes - Crushproof case - 1060 Micro Case Accessories

Cat. #	Description