



ENGLISH

Datasheet

RS Pro 5mm Pitch Straight PCB Terminal Block with Screw Clamp Termination, Through Hole, 24 Way

RS Stock No: **494-8899**



Product Details

RS Pro 24-way 5 mm pitch straight PCB terminal block with screw clamp termination, features through hole mounting type. A range of stackable PCB mounting terminals have beryllium copper spring contacts and receptacles to mate with PCB header strip on a 5 mm pitch. The PCB header required is obtainable in a strip 24 pin long which can be easily broken to length required. These Stackable PCB mounting Terminals are rated at 10 A/250 V.

Specifications:

Body Orientation	Straight
Current Rating	10 A
Depth	10.8 mm
Gender	Male
Length	120 mm
Material	Nylon 66
Mounting Type	Through Hole
Number of Contacts	24
Number of Rows	1
Pitch	5 mm
Termination Method	Screw Clamp
Type	Plug
Voltage Rating	300 V
Width	13.5 mm
Insulation Resistance	1000 mΩ
American Wire Gauge	14 to 20 AWG
Insulation Withstand Voltage	1500 V ac
Operating Temperature Range	-40 to +105°C
Flammability Rating	UL 94 V-0