





- | | | | | |
|---|------------|---|---------------|------------|
| 7 | 3.50[.137] |  | YES | 1-207530-1 |
| | 4.60[.181] |  | NO | 1-207530-0 |
| | |  | YES | 207530-9 |
| | |  | NO | 207530-8 |
| | |  | YES | 207530-7 |
| | |  | NO | 207530-4 |
| | |  | YES | 207530-3 |
| | |  | NO | 207530-2 |
| | |  | YES | 207530-1 |
| | DIM A | CONTACT FINISH | MOUNTING TABS | PART NO |

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 03/19/92		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
		L.SIPE			
		CHK 3-25-92			
		R.STONE			
DIMENSIONS: mm [INCHES]		APVD 3-25-92		NAME	
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SOCKET HEADER ASSEMBLY, 18 POSITION, METRIMATE	
		0 PLC ± -			
		1 PLC ± -			
		2 PLC ± 0.25 [0.010]			
3 PLC ± -		PRODUCT SPEC			
4 PLC ± -		108-10033			
ANGLES ± -		APPLICATION SPEC			
MATERIAL		—		SIZE	CAGE CODE
FINISH		WEIGHT —		A2	00779
HOUSING: 		CONTACT: SEE TABLE		DRAWING NO	
				C-207530	
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 of 1
				REV	M1