


Housing - HC-B 6-KML-73/O1M20 - 1604719

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

HEAVYCON coupling housing B6, with single locking latch, height 73 mm, with support 1x M20



Key commercial data

Packing unit	10 pc
GTIN	 4 017918 881634
Weight per Piece (excluding packing)	205.59 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Height	73 mm
Width	43 mm
Length	60 mm

Ambient conditions

Degree of protection of housing (IP)	IP65
--------------------------------------	------

General

Note	For contact inserts HC-B6, BB10, DD24, M
Type	B6
Housing type	Coupling housings
Locking type	With single locking latch
No. of cable exits	1
Cable exit	Straight
Type of the screw connection	1x M20
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Seal material	NBR

Housing - HC-B 6-KML-73/O1M20 - 1604719

Technical data

General

Material lock	Stainless steel, handle: PA
Material grip body interlock	PA-GF

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

Housing - HC-B 6-KML-73/O1M20 - 1604719

Approvals



Drawings

Dimensioned drawing

