




(0,635mm) .025"

SOLC SERIES



# QUAD ROW SMT SOCKET

## SPECIFICATIONS

For complete specifications and recommended PCB layouts see [www.samtec.com?SOLC](http://www.samtec.com?SOLC)

**Insulator Material:**  
Black Liquid Crystal Polymer



**Contact Material:**  
Phosphor Bronze

**Plating:**  
Au over 50µ" (1,27µm) Ni

**Current Rating:**  
2.5A @ 80°C ambient

**Operating Temp Range:**  
-55°C to +125°C

**Contact Resistance:**  
10 mΩ max

**Insertion Depth:**  
(1,68mm) .066" to (3,61mm) .142" with (0,38mm) .015" wiper

**Insertion Force:**  
(Single contact only)  
2.0oz (0,56N) average

**Normal Force:**  
75 grams (0,74N) average

**Withdrawal Force:**  
(Single contact only)  
1.5oz (0,42N) average


**Max Cycles:**  
100+

**RoHS Compliant:**  
Yes


**Processing:**  
Lead-Free Solderable:  
Yes

**SMT Lead Coplanarity:**  
(0,10mm) .004" max (05-35)  
(0,15mm) .006" max (40-50)

Mates with:  
TOLC



05, 10, 15, 20, 25,  
30, 35, 40, 45, 50  
(Call Samtec for other sizes)



**-F**  
= Gold flash on contact,  
Gold flash on tail

**-L**  
= 10µ" (0,25µm) Gold on contact,  
Gold flash on tail

Note: Other Gold plating options available. Contact Samtec.

**-A**  
= Alignment Pin (N/A with -LC)

**-LC**  
= Locking Clip (N/A with -A) (Manual placement required)


**-K**  
= (7,00mm) .276" DIA Polyimide film Pick & Place Pad

**-P**  
= Pick & Place Pad

**-TR**  
= Tape & Reel

## ALSO AVAILABLE

- For Micro Rugged, see the MOLC/FOLC pages located in the Tiger Eye™ section.



Note: Some sizes, styles and options are non-standard, non-returnable.

**TAPE & REEL AVAILABILITY**

No tooling charges.  
Minimum order is the lesser of a full reel quantity or 125 pieces. Order any quantity above minimum. In-house design, manufacture. Quick turn-around.  
Call Samtec for specifications and ordering information.

Due to technical progress, all designs, specifications and components are subject to change without notice.

[WWW.SAMTEC.COM](http://WWW.SAMTEC.COM)