

3-Wire *microfast*® Cordsets, Standard Duty

- Straight Male Connectors
- NEMA 1, 3, 4, 6P and IEC IP 67 Protection
- 250 V, 4.0 A



Housing Style	Part Number	Cable	Features	Pinout	
 	SB 3T-*	AWM PVC Yellow 3x22 AWG 105°C 5.2 mm OD Cable #RF50531- <sup>†</sup> M <sup>†</sup>	<i>flexlife</i> ®		
	SB 3T-*/S90	AWM PUR Yellow 3x18 AWG 80°C 5.7 mm OD Cable #RF50547- <sup>†</sup> M <sup>†</sup>	<i>Cut/Abrasion Immune</i>	1. GN 2. RD/BK 3. RD/WH	
	SB 3T-*/S105	AWM PVC Yellow 3x22 AWG 105°C 5.7 mm OD Cable #RF50535- <sup>†</sup> M <sup>†</sup>	<i>Braided Copper Shield</i>		
	SB 3T-*/S749	AWM PVC Yellow 2x22 AWG 105°C 5.2 mm OD Cable #RF50650- <sup>†</sup> M <sup>†</sup>	<i>3-pin with 2 conductors</i>	1. N/C 2. BK 3. WH	
	SB 3T-*/S1507	AWM TPE Grey 3x20 AWG 105°C 5.7 mm OD Cable #RF50940- <sup>†</sup> M <sup>†</sup>	<i>Flexlife-10, High Flex - Over 10 million cycles</i>	1. BK 2. BN 3. BU	
	SB 3T-*/X0R	AWM PVC Yellow 3x18 AWG 80°C 250°C short term 5.7 mm OD Cable #RF04159- <sup>†</sup> M <sup>†</sup>	<i>Weld Flash Immune, High Temp Immune</i>	1. GN 2. RD 3. RD/WH	

\* Length in meters. Standard cable lengths are 2, 4, 6, 8 and 10 meters. Consult factory for other lengths.

\*\* Standard coupling nut material is nickel plated brass "SB .."; "SBK .." indicates nylon and "SBV .." indicates 316 stainless steel.

<sup>†</sup> See Section N for *reelfast*® cable information.