

RefLED+ ES50

RefLED+ ES50 4.5W 230LM 827 40° SL

0026379



Range features

- Up to 87% energy saving compared to halogen lamps
- 4.5W true 35W halogen retrofit, 6.5W true 45W halogen retrofit, 7.5W true 50W halogen retrofit
- As per IEC standard dimensions, its compact size means it can retrofit all GU10 and GZ10
- Beam angle of 40°
- Available in different colour temperatures: 2700K Homelight, 3000K Warm white and 4000K Cool white
- High efficacy, up to 51lm/W
- High light output, up to 345lm
- Average rated life of 15,000 hours
- The new brilliant white finish complements domestic lighting
- Power Factor = 0.5



PRODUCT OVERVIEW

Ordering number	0026379
Light colour	827 Homelight
Technology	LED
Energy class	A+
Average life (Rated) (h)	15000
Lamp shape	Reflector
Lamp finish	White
Dimmable	No
Cap/Base	GU10
Type	REFLED+ ES50
EAN code	5410288263793
CRI (Ra)	80
Beam angle(°)	40
Beam angle(°)	40
Colour temperature (K)	2700
Useful luminous flux (Rated) (lm)	230
Efficacy (Rated) (lm/w)	51.1
Watt (Nominal) (W)	4.5
Equivalent watt (W)	35
Voltage (V)	220-240

TECHNICAL DRAWINGS

