

Support rollers with axial guidance



Dimensions			Basic load ratings		Fatigue load limit	Maximum radial loads		Limiting speed	Mass	Designation
D	d	C	dynamic C	static C ₀	P _u	dynamic F _r	static F _{0r}			
mm			kN		kN	kN		r/min	kg	-
52	25	24	14,7	25,5	3,1	21,6	31	2400	0,28	NATR 25 PPA

