



Sample photo

**Order symbol:** P 121209  
**Product nbr:** 7094220  
**Description:** Enclosure  
**Remarks:** Polyester

**EAN:** 6418074004376  
**El. number:**  
 Finland 3423660  
 Denmark 8212005646  
 Italy 7331030  
 Sweden 2536215

**Including:** Base, cover with EPDM gasket and stainless steel cover screws.

| Dimensions:            |  | L                      | W   | H   | Rating:                                    |
|------------------------|--|------------------------|-----|-----|--------------------------------------------|
| mm:                    |  | 120                    | 122 | 90  | Ingress Protection (EN 60529): IP 66/67    |
| inch:                  |  | 4.7                    | 4.8 | 3.5 | Impact Resistance (EN 50102): IK 08        |
| Materials:             |  |                        |     |     | Electrical insulation: Totally insulated   |
| Material:              |  | GRP                    |     |     | Halogen free (DIN/VDE 0472, Part 815): Yes |
| Base colour:           |  | RAL 7001               |     |     | UV resistance: UL 508                      |
| Cover colour:          |  | RAL 7001               |     |     | Flammability Rating (UL 746 C 5): UL 94 5V |
| Cover screws material: |  | Stainless steel        |     |     | Glow Wire Test (IEC 695-2-1) °C: 960       |
| Gasket material:       |  | EPDM                   |     |     | NEMA Class: NEMA 1, 4, 4X, 12, 13          |
| Temperatures:          |  |                        |     |     | Certificates:                              |
| Short term:            |  | -50 ... 120 °C         |     |     |                                            |
| Continuous:            |  | -40 ... 80 °C          |     |     |                                            |
| Short term:            |  | -60 ... 250 °F         |     |     |                                            |
| Continuous:            |  | -40 ... 175 °F         |     |     |                                            |
| Accessories:           |  |                        |     |     |                                            |
| AM 1212                |  | Mounting plate         |     |     |                                            |
| ARH 12                 |  | DIN-35 Mounting rail   |     |     |                                            |
| MRS 28541              |  | Wall fastening lug set |     |     |                                            |
| PH A & AH A/B          |  | Hinge set              |     |     |                                            |

