

UFR100x34-Ø12 blue

EAN 4031582070392

Wheel centre made of Polyamide, Tread: elastic-tyre, non-marking, roller bearing

Technical Data	
Wheel diameter	100 mm
Width of Tread	34 mm
Axle Hole Ø	12 mm
Hub length	44.4 mm
Temperature	- 20 / + 80 °C
Standard	EN 12532
Weight	0.352 kg
Dynamic Load capacity	160 kg
Static Load capacity	320 kg
Hardness of tread	A 64 Shore



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

