

Datasheet

RS 4 Core Unscreened Industrial Cable, PVC Sheath, 250 V, 2.8mm OD, 0.055 mm² CSA 0.25 A, 25m

Stock Number - 660-3977



Description:

Rated Temperature (oC): -20 ~ 80

Rated Voltage (V):250

Flammability Test: IEC60332-1



ENGLISH

Construction:

Conductor: Tinned Copper

Conductor Dia. (mm): $0.10 \pm 0.008 \times 7$

Insulation: PVC

Insulation Dia. (mm): $0.7 \pm 0.05 \times 4C$

Tape: Mylar Spiral

Coverage: $\geq 115\%$

ID Thread : Green, White/Green

A rip cord : 210 D

Jacket: FR-PVC

Outer Dia. (mm): 2.6 ± 0.1

Colour:

The colour of the insulation: Red , Blue
, Green , Yellow

The jacket colour: Black

Marking(3times/m):

RS 6603977 7 - 1 – 4A

Performance:**Electrical Characteristics:****Max.Conductor DC Resistance at 20°C (Ω /Km) :**

<384

Min.Insulation DC Resistance at 20°C ($M\Omega$ *KM) :

>200

Current Rating : 0.25 A