

Passive module - VIP-2/PT/FLK50/S7/A-S400 - 2904289

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




VARIOFACE interface module, for I/Os of the SIMATIC® S7-400, with SIMATIC®-specific marking, only in conjunction with FLKM 50-PA-S400

The figure shows a version with MODICON® TSX Quantum marking and screw connection



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 813754
Weight per Piece (excluding packing)	224.1 g
Custom tariff number	85369010
Country of origin	United States
Note	Made to Order (non-returnable)

Technical data

Dimensions

Width	107.9 mm
Height	72.1 mm
Depth	56 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Max. permissible operating voltage	60 V AC/DC
Max. perm. current (per branch)	1 A
Number of positions	50
Status display	No

Passive module - VIP-2/PT/FLK50/S7/A-S400 - 2904289

Technical data

General

Mounting position	any
Standards/regulations	IEC 60664
	DIN EN 50178
	IEC 62103
Rated surge voltage	0.6 kV
Pollution degree	2
Surge voltage category	II

Connection data for connection 1

Connection name	Field level
Connection method	Push-in connection
Conductor cross section solid min.	0.14 mm ²
Conductor cross section solid max.	2.5 mm ²
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm

Connection data for connection 2

Connection name	Controller level
Number of connections	1
Connection method	IDC/FLK pin strip (2.54 mm)
Number of positions	50

Supported controller

Controller	SIEMENS S7-400
- suitable I/O card	6ES7 421-1BL01-0AA0
	6ES7 421-7BH01-0AB0
	6ES7 421-7DH00-0AA0
	6ES7 422-1BL00-0AA0
	6ES7 422-7BL00-0AB0

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27141152

Passive module - VIP-2/PT/FLK50/S7/A-S400 - 2904289

Classifications

eCl@ss

eCl@ss 8.0	27141152
------------	----------

ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Approvals

Approvals


Approvals

CSA / UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

	
mm ² /AWG/kcmil	26-14
Nominal current I _N	1 A
Nominal voltage U _N	125 V

Passive module - VIP-2/PT/FLK50/S7/A-S400 - 2904289

Approvals

UL Recognized	
mm ² /AWG/kcmil	26-14
Nominal current I _N	1 A
Nominal voltage U _N	125 V

cUL Recognized	
mm ² /AWG/kcmil	26-14
Nominal current I _N	1 A
Nominal voltage U _N	125 V

EAC

cULus Recognized	
------------------	--

Accessories

Accessories

Printing system

Printer - BLUEMARK X1 - 5147777



Printers with UV technology for printing plastic labels in UniCard format.

System cable

Cable - FLK 50/EZ-DR/ 50/KONFEK - 2289065



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 0.5 m

Passive module - VIP-2/PT/FLK50/S7/A-S400 - 2904289

Accessories

Cable - FLK 50/EZ-DR/ 100/KONFEK - 2289078



Round cable sets, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 1 m

Cable - FLK 50/EZ-DR/ 150/KONFEK - 2289081



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 1.5 m

Cable - FLK 50/EZ-DR/ 200/KONFEK - 2289094



Round cable sets, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 2 m

Cable - FLK 50/EZ-DR/ 250/KONFEK - 2289104



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 2.5 m

Cable - FLK 50/EZ-DR/ 300/KONFEK - 2289117



Round cable sets, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 3 m

Passive module - VIP-2/PT/FLK50/S7/A-S400 - 2904289

Accessories

Cable - FLK 50/EZ-DR/ 350/KONFEK - 2289120



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 3.5 m

Cable - FLK 50/EZ-DR/ 400/KONFEK - 2289133



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 4 m

Cable - FLK 50/EZ-DR/ 450/KONFEK - 2289573



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 4,5 m

Cable - FLK 50/EZ-DR/ 500/KONFEK - 2289586



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 5 m

Cable - FLK 50/EZ-DR/ 550/KONFEK - 2289599



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 5,5 m

Passive module - VIP-2/PT/FLK50/S7/A-S400 - 2904289

Accessories

Cable - FLK 50/EZ-DR/ 600/KONFEK - 2289609



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 6 m

Cable - FLK 50/EZ-DR/ 650/KONFEK - 2289612



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 6.5 m

Cable - FLK 50/EZ-DR/ 700/KONFEK - 2289625



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 7 m

Cable - FLK 50/EZ-DR/ 750/KONFEK - 2289638



Round cable set, with two 50-pos. female connectors (1:1 connection), for connecting 32 channels, cable length: 7.5 m

Cable - FLK 50/EZ-DR/ 800/KONFEK - 2289641



Round cable sets, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 8 m

Passive module - VIP-2/PT/FLK50/S7/A-S400 - 2904289

Accessories

Cable - FLK 50/EZ-DR/ 850/KONFEK - 2289654



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 8.5 m

Cable - FLK 50/EZ-DR/ 900/KONFEK - 2289667



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 9 m

Cable - FLK 50/EZ-DR/ 950/KONFEK - 2289670



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 9.5 m

Cable - FLK 50/EZ-DR/1000/KONFEK - 2289683



Round cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 10 m

Cable - FLK EZ-DR.../.../... - 2295059



Round cable, with preassembly, not shielded, variable cable length

Passive module - VIP-2/PT/FLK50/S7/A-S400 - 2904289

Accessories

Cable - FLK 50/EZ-DR/ 50/KONFEK/S - 2299097



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 0.5 m

Cable - FLK 50/EZ-DR/ 100/KONFEK/S - 2299107



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 1 m

Cable - FLK 50/EZ-DR/ 150/KONFEK/S - 2299110



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 1.5 m

Cable - FLK 50/EZ-DR/ 200/KONFEK/S - 2299123



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 2 m

Cable - FLK 50/EZ-DR/ 300/KONFEK/S - 2299136



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 3 m

Passive module - VIP-2/PT/FLK50/S7/A-S400 - 2904289

Accessories

Cable - FLK 50/EZ-DR/ 400/KONFEK/S - 2299149



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 4 m

Cable - FLK 50/EZ-DR/ 600/KONFEK/S - 2299152



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 6 m

Cable - FLK 50/EZ-DR/ 800/KONFEK/S - 2299165



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 8 m

Cable - FLK 50/EZ-DR/1000/KONFEK/S - 2299178



Round shielded cable set, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels, cable length: 10 m

Cable - FLK EZ-DR-S.../.../... - 2295046



Round cable, with preassembly, shielded, variable cable length

Passive module - VIP-2/PT/FLK50/S7/A-S400 - 2904289

Accessories

Cable - CABLE-FLK50/0,14/HF/ 0,5M - 2314134



Assembled halogen-free round cable, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels. Halogen-free refers exclusively to the 50-pos. cable. Length of cable: 0.55 yd

Cable - CABLE-FLK50/0,14/HF/ 1,0M - 2314147



Assembled halogen-free round cable, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels. Halogen-free refers exclusively to the 50-pos. cable. Length of cable: 1 m

Cable - CABLE-FLK50/0,14/HF/ 1,5M - 2314150



Assembled halogen-free round cable, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels. Halogen-free refers exclusively to the 50-pos. cable. Length of cable: 1.64 yd

Cable - CABLE-FLK50/0,14/HF/ 2,0M - 2314163



Assembled halogen-free round cable, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels. Halogen-free refers exclusively to the 50-pos. cable. Length of cable: 2.19 yd

Cable - CABLE-FLK50/0,14/HF/ 2,5M - 2314176



Assembled halogen-free round cable, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels. Halogen-free refers exclusively to the 50-pos. cable. Length of cable: 2.73 yd

Passive module - VIP-2/PT/FLK50/S7/A-S400 - 2904289

Accessories

Cable - CABLE-FLK50/0,14/HF/ 5,0M - 2314202



Assembled halogen-free round cable, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels. Halogen-free refers exclusively to the 50-pos. cable. Length of cable: 5 m

Cable - CABLE-FLK50/0,14/HF/ 6,0M - 2314215



Assembled halogen-free round cable, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels. Halogen-free refers exclusively to the 50-pos. cable. Length of cable: 6 m

Cable - CABLE-FLK50/0,14/HF/ 7,0M - 2314228



Assembled halogen-free round cable, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels. Halogen-free refers exclusively to the 50-pos. cable. Length of cable: 7 m

Cable - CABLE-FLK50/0,14/HF/ 8,0M - 2314231



Assembled halogen-free round cable, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels. Halogen-free refers exclusively to the 50-pos. cable. Length of cable: 8 m

Cable - CABLE-FLK50-0,14-HF/... - 2314257



Assembled halogen-free round cable, with two 50-pos. socket strips (1:1 connection), for connecting 32 channels. Halogen-free refers exclusively to the 50-pos. cable. Length of cable: Variable

Terminal marking

Passive module - VIP-2/PT/FLK50/S7/A-S400 - 2904289

Accessories

Marker for terminal blocks - UC-TM 4 - 0818111



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 4.2 mm, Lettering field: 3.6 x 10.5 mm

Marker for terminal blocks - UC-TM 6 - 0818085



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 6.2 mm, Lettering field: 5.6 x 10.5 mm

Zack marker strip - ZB 5,08:UNBEDRUCKT - 0809793



Zack marker strip, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 5.08 mm, Lettering field: 4.98 x 10.5 mm

Zack marker strip - ZB 22:UNBEDRUCKT - 0811862



Zack marker strip, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Snap into tall marker groove, for terminal block width: 22 mm, Lettering field: 10.5 x 21.8 mm

Drawings

Circuit diagram

