

PocketScope I DS1M12 USB oscilloscope, 250 kHz

Item No.: ds1m12



The 2-channel USB "pocket scope"

This USB scope is small, low-cost and easy to use. It is suitable for education, experiment and mobile applications. With the Windows software included, the module also works as a datalogger, spectrum analyzer, voltmeter and frequency meter.

- Oscilloscope, datalogger, spectrum analyzer, voltmeter, frequency meter and simple waveform generator in one device.
- A/D resolution 12 bit.
- 2 channels with BNC for standard probes. Third BNC shared as trigger input or waveform generator.
- Simultaneous sampling on both channels.
- 32 kB waveform buffer.
- 20 MS/s sampling rate (repetitive), 1 MS/s native.
- Max. input voltage ± 50 V.
- AC/DC coupling.
- Trigger modes: Edge, min./max. pulse width and delay trigger.

- Analog bandwidth 250 kHz.
- Built-in, simple 10 bit waveform generator with 3.5 V output range and 1 k buffer.
- USB-powered (250 mA). USB 1.1/2.0 fullspeed.
- Dimensions only approx. 116 mm (W) x 30 mm (H) x 100 mm (D), 160 g (without cable).

Included 2-channel scope for USB, CD, USB cable.

Software: Windows driver and Software EasyScope II and EasyLogger.

Model overview

Model	PocketScope I (DS1M12)	PocketScope II (DS60M10)
Functions	Oscilloscope/DSO, datalogger, spectrum analyzer, volt meter, frequency meter	
Channels	2 simultaneous channels; input voltage max. ± 50 V; AC/DC coupling	
Resolution	12 bit	10/8 bit
Bandwidth	250 kHz	5 MHz
Sample rate	20 MS/s (repetitive/ETS), 1 MS/s native	Oscilloscope max. 60 MS/s simultaneous on both channels, datalogger up to 1 KS/s
Connectors	3x BNC: Channel A, channel B, trigger input/waveform generator (resolution 10 bit, ± 3.5 V output range, 1 k buffer)	3x BNC: Channel A, channel B, trigger input/compensation output
Interface	USB 2.0 fullspeed (compatible with USB 1.1), USB-powered	
Dimensions (mm)	Approx. 116 x 30 x 100	
Software	EasyScope II and EasyLogger	EasyScope III oscilloscope and datalogger software